

Brand Name: Lenovo
Colour: Black
DisplayPort: Yes
Environmentally Friendly: Yes
Form Factor: Small Form Factor
Graphics Controller: Intel
Manufacturer:
Graphics Controller Model: HD Graphics 530
Graphics Memory Accessibility: Shared
Graphics Memory Technology: DDR4 SDRAM
Green Compliant: Yes
Monitor Included: No
Number of USB 2.0 Ports: 2
Number of USB 3.0 Ports: 4
Operating System Architecture: 64-bit
Operating System Platform: Windows
Operating System: Windows 10 Pro
Optical Drive Type: DVD-Writer
Processor Manufacturer: Intel
Processor Model: i3-6100
Processor Speed: 3.70 GHz
Processor Type: Core i3
Product Family: S510
Product Type: Desktop Computer
Screen Size: No
Standard Memory: 4 GB
Total Hard Drive Capacity: 500 GB
Total Number of USB Ports: 6
VGA: Yes
Wireless LAN: No

Camera

Screen Size: No

Display & Graphics

Graphics Controller: Intel
Manufacturer:
Graphics Controller Model: HD Graphics 530
Graphics Memory Accessibility: Shared
Graphics Memory Technology: DDR4 SDRAM
Monitor Included: No
Screen Size: No

General Information

Brand Name: Lenovo
Manufacturer Part Number: 10KY000DUK
Manufacturer Website Address: <http://www.lenovo.com/uk/en/>
Manufacturer: Lenovo Group Limited
Package Contents:

- S510 10KY000DUK Desktop Computer
- Keyboard
- Mouse

Product Model: 10KY000DUK
Product Name: S510 10KY000DUK Desktop Computer
Product Series: S510
Product Type: Desktop Computer

Interfaces/Ports

DisplayPort: Yes
Number of USB 2.0 Ports: 2
Number of USB 3.0 Ports: 4
Total Number of USB Ports: 6
VGA: Yes
Wireless LAN: No

Memory

Memory Technology: DDR4 SDRAM
Standard Memory: 4 GB

Miscellaneous

Environmental Certification: ENERGY STAR 6.1
Environmentally Friendly: Yes
Features: Security Slot

Form Factor:	Small Form Factor
Green Compliance Certificate/Authority:	ENERGY STAR 6.1
Green Compliant:	Yes
Monitor Included:	No
Package Contents:	<ul style="list-style-type: none">• S510 10KY000DUK Desktop Computer• Keyboard• Mouse

Network & Communication

Wireless LAN:	No
---------------	----

Physical Characteristics

Colour:	Black
Depth:	320 mm
Form Factor:	Small Form Factor
Height:	88.9 mm
Weight (Approximate):	4.13 kg
Width:	294.6 mm

Processor & Chipset

Processor Generation:	6th Gen
Processor Manufacturer:	Intel
Processor Model:	i3-6100
Processor Speed:	3.70 GHz
Processor Type:	Core i3

Product Information

Features:	Security Slot
Form Factor:	Small Form Factor
Operating System Platform:	Windows
Screen Size:	No
Width:	294.6 mm

Software

Operating System Architecture:	64-bit
Operating System Platform:	Windows
Operating System:	Windows 10 Pro

Storage

Features:	Security Slot
Optical Drive Type:	DVD-Writer
Optical Media Supported:	DVD-RAM/±R/±RW
Total Hard Drive Capacity:	500 GB

Technical Information

Features:	Security Slot
Memory Technology:	DDR4 SDRAM
Operating System:	Windows 10 Pro
Optical Drive Type:	DVD-Writer
Optical Media Supported:	DVD-RAM/±R/±RW
Processor Generation:	6th Gen
Processor Manufacturer:	Intel
Screen Size:	No
Wireless LAN:	No

Video

Graphics Controller Manufacturer:	Intel
Graphics Controller Model:	HD Graphics 530
Graphics Memory Accessibility:	Shared
Graphics Memory Technology:	DDR4 SDRAM

Warranty

Limited Warranty:	1 Year
-------------------	--------

Wireless Specifications

Features:	Security Slot
Wireless LAN:	No