

# Doro 5030

## CLASSIC DESIGN. EASY FUNCTIONALITY.

Doro 5030 is a good-looking phone bringing you widely spaced, convex keys, predictive text, direct memories and an SMS button for easy dialling and texting. A crisp colour display and enhanced sound simplify usage even more. Other practical features include a torch, reminders, wake-up alarm, vibrating ringer and Assistance button.

- Extra loud and clear sound
- Separated, high contrast keys
- Assistance button for extra safety



Torch



Assistance button

### Top features

Torch	✓
Visual ring indicator	✓
Assistance button	✓
Speakerphone	✓

### Main features

Calculator	✓
Wake up alarm	✓
FM-radio	✓
Key tone	✓
Keylock	✓
Calendar with reminder	✓
Calendar	✓
Backlit keypad	✓
Daily reminder	✓
Startup wizard	✓
ICE (In Case of Emergency)	✓

### Memories

Phonebook positions	100
List top 10 contacts first	✓
Call log positions	60
One touch memories	2

### Handset unit display

Resolution (H x W pixels)	128*160
Customisable wallpaper	✓
Colour display	✓
Display size (H x W inch)	1.7
Display size (H x W mm)	28*35
Big display text	✓
Adjustable font size	✓

### SMS

SMS	✓
SMS key	✓
Predictive text	✓

### Sounds & Signals

Polyphonic ringtones	4
Ringer volume settings except off	7
Vibrating ringer	✓
Ringer off setting	✓

### Acoustics

Volume settings	7
Microphone mute	✓
Tone control	✓
Maximum ringer volume (dB(A) at 1 metre)	>83
Hearing Aid Compatibility Rating	T4/M3

### Ergonomics

Handset size (mm)	117*53*14
Handset weight including batteries (g)	78

### Cables & Connections

Headset outlet (3.5mm)	✓
------------------------	---

### Powering handset unit

AC Adapter spec V/mA	5V/500mA
Battery included (type)	800mAh Li-ion
Talk time (up to hours)	9
Standby time (up to hours)	530

### Technology

SAR (head)	0.58
GSM (band)	900/1800/1900
Micro-SIM (3FF)	✓
Bluetooth®	✓
Bluetooth® protocoll	3.0
SAR (body)	0.88