
PARATHOM PRO AR111 75 24° 12.5 W/827 12 V G53

PARATHOM PRO LEDspot 111 | LED reflector lamps AR111 with retrofit pin base



Areas of application

- Shops
- Galleries
- Museums
- Shops and exhibition rooms
- Directional light sources

Product benefits

- Very low energy consumption
- Extremely long life
- Robust against vibrations
- No UV and near-IR radiation in the light beam
- Efficient generation of white light

Product features

- Professional LED lamp
- Dimmable (with many common dimmers, see also www.osram.com/dim)
- Lifetime: up to 45,000 h
- Mercury-free lamps
- High color consistency
- Made in Germany



Technical data

Electrical data

Rated wattage	12.50 W
Nominal wattage	12.50 W
Nominal voltage	12.0 V
Claimed equiv. conventional lamp power	75 W
Operating frequency	50...60 Hz
Power factor λ	0.92

Photometrical data


Luminous intensity	4800 cd
Nominal luminous flux	740 lm
Rated luminous flux	740 lm
Color temperature	2700 K
Color rendering index Ra	≥ 80
Light color (designation)	Warm White
Standard deviation of color matching	≤ 4 sdc _m
Nominal useful luminous flux 90°	740 lm
Rated useful luminous flux 90°	740 lm
Rated peak intensity	5000 cd

Light technical data

Beam angle	24 °
Warm-up time (60 %)	≤ 0.50 s
Starting time	≤ 0.5 s
Nominal beam angle	24 °
Rated beam angle (half peak value)	24.00 °

Product datasheet

Dimensions & weight



Overall length	58.5 mm
Diameter	111.0 mm
Outer bulb	AR111
Length	58.5 mm
Maximum diameter	111.0 mm

Lifespan

Nominal lamp life time	45000 h
Rated lamp life time	45000 h
Number of switching cycles	1000000
Lumen main.fact.at end of nom.life time	0.70

Additional product data

Base (standard designation)	G53
Mercury-free	Yes
Appropriate disposal acc. to WEEE	Yes
Product remark	All technical parameters apply to the entire lamp/Due to the complex production process for light-emitting diodes, the typical values shown for the technical LED parameters are purely statistical values that do not necessarily match the actual technical parameters of each individual product, which can vary from the typical value

Capabilities

Dimmable	Yes ¹⁾
-----------------	-------------------

¹⁾ With many common dimmers

Certificates & standards


Product datasheet

Energy efficiency class	A
Energy consumption	14 kWh/1000h

Country specific categorizations

ILCOS	DRR-12,5-12-G53-111/24
Order reference	PPAR111 7524 12

Light Distribution



Spectral power distribution



Guarantee

Equipment / Accessories

Product datasheet

Suitable for many commercially available electronic or conventional transformers

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4052899907812	PARATHOM PRO AR111 75 24° 12.5 W/827 12 V G53	Shipping carton box 6	275 mm x 185 mm x 130 mm	6.61 dm ³	1341.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

References / Links

For dimming conformity see

▶ www.osram.com/DIM

For Guarantee see

▶ www.osram.com/guarantee

For further products and actual information concerning LED lamps see

▶ www.osram.com/ledlamps

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.