

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0191640034**
Status: **Active**
Overview: Perma-Seal™ Terminals
Description: Perma-Seal™ Ring Tongue Terminal for 14-16 AWG Wire, Stud Size 10 (M5)

Documents:

Drawing (PDF)	Product Specification PS-19902-013 (PDF)
Product Specification PS-19902-011 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Ring and Spade Terminals
Series	<u>19164</u>
Crimp Quality Equipment	Yes
Mil-Spec	N/A
MolexKits	Yes
Overview	<u>Perma-Seal™ Terminals</u>
Product Name	Perma-Seal™
Type	Ring
UPC	800753113220

Physical

Barrel Type	Closed
Insulation	NiAc™
Material - Plating Mating	Tin
Net Weight	1.161/g
Packaging Type	Bag
Stud Size	10 (M5)
Wire Insulation Diameter	5.97mm
Wire Size AWG	14, 16
Wire Size mm²	1.23-1.94

Material Info

Engineering Number	SB-237-10
--------------------	-----------

Reference - Drawing Numbers

Product Specification	PS-19902-011, PS-19902-013
Sales Drawing	SD-19164-026



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

19164 Series

Application Tooling | FAQ

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description	Product #
PremiumGrade™	<u>0640017400</u>
Hand Crimp Tool	
Power Crimp Tool	<u>0640057400</u>
Head for Terminals 10-22 AWG Wire	

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION