

Auxiliary Contact Block



RAS-BCBNO



RAS-CBNO



RAS-BCBNC



RAS-CBNC

General Characteristics:


Products	: Push Buttons, Selector Switches, Latching Mushroom Head Push Buttons, Pilot Lights & Illuminated Push Buttons
Reference Standard	: IEC 60947-5-1, EN 60947-5-1, IEC 337-1
Protection Degree	: IP 65/IP 66 according to IEC 60947-1; NEMA4, 4X
Pollution Degree	: 3
Temperature	: -40°C to +70°C (Storage) -25°C to +70°C (Working)
Vibration Resistance	: Mushroom Head Push Buttons: 8g, Other Push Buttons & Pilot Lights: 15g (40 to 500Hz) confirming to IEC 68-2-6
Shock Resistance conforming to IEC 68-2-27	: Push Buttons: 70g, Mushroom Head Push Buttons: 15g, Selector Switches: 200g
Working Position	: All Working Position are Allowed
Mechanical Life	: Push Buttons & Selector Switches 1 million Operations, Emergency Mushroom Push Buttons 300,000 Operations

Contact elements Characteristics:

Rated Thermal Current I_{th}	: 10A
Rated Insulation Voltage U_i	: 500V Conforming to IEC 60947-1
Insulation Category	: Group C conforming to NF C 20-040, VDE 0110
Operating Force	: Push Buttons – 1 'NO' = 10N, 1 'NC' = 8N Additional Contacts – 'NO' = +5N, 'NC' = +3N
Dielectric Strength	: 2.5kV for 1 minute
Insulation Resistance	: 2M Ω min (500V DC)
Initial Contact Resistance	: \leq 25m Ω
Short Circuits Protection	: 10A 500V, Cartridge Fuse g1 or N Conforming to IEC 337-1
Terminal Reference	: Conforming to CENELEC EN 50013
Connections	: On Screw to losable plate lamp Sec. 2.5mm ² max. (14AWG)
Contact Operation	: Self Cleaning Type, Slow Action, Positive Opening
Operation Frequency	: 3,600 Operation per hour
Utilization Category	: AC 15 (DC 13)
Rated Power	DC Supply
Conforming to IEC 60947-5-1	Power Broken in Watts
Load Factor: 0.5	for 1 million Operations

AC Supply (50/60Hz)	<u>Voltage</u>	24V	48V	120V
	Inductive Load	65W	48W	40W

Auxiliary Contact Block



AC Ratings, Inductive – NEMA A600

35% Power Factor

Volts	Make Amperes	VA	Break Amperes	VA	Continuous Carrying Amperes	Resistive 75% Power Factor Make, Break & Continuous Amperes
120	60	7,200	6	720	10	10
240	30		3			
480	15		1.5			
600	12		1.2			

DC Ratings, NEMA Type Q600

Inductive and Resistive

Volts	Make & Break (Amp)	Continuous (Amp)
125	0.55	2.5
250	0.27	
600	0.1	

Part Number Table

Description	Part Number
Contact Block, 1NO	RAS-CBNO
Contact Block, 1NC	RAS-BCBNC
22mm Switches N/C Block	RAS-CBNC
22mm Switches N/O Block	RAS-BCBNO

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

