

RF333

Description & Specification

Features

- Compact keyboard with mini mouse
- 2.4GHz RF Wireless
- up to 10m support
- Nano wireless receiver
- All batteries supplied

Keyboard features

Comfortable and durable super slim keycaps

Compatible with Windows XP/2000/Vista/7

Silicone cover supplied for the keyboard

Mouse features

- 3 button optical mouse

- convenient scroll wheel

- 1000/1600/2400dpi high resolution

- super mini 2.4ghz nano receiver stored in the battery compartment

| | |
|----------------------------|--------------------------|
| Button Life: | 10 Million Cycles (MBTF) |
| Key Travel: | 3.5 ± 0.5mm |
| Operating Force: | 55g ± 20g |
| Supply Voltage: | 4.40V ~ 5.20V |
| Working Current: | <50mA |
| Storage temp: | -20°C ~ +60°C |
| Operating Temp: | -5°C ~ +45°C |
| Storage Humidity: | 10% ~ 70% RH |
| Operating Humidity: | 10% ~ 80% RH |