

LM888

Classic 3 button mouse

- Elegant design & soft touch keys
- 1200dpi sensor
- 1.5m cable length
- Compatible with Windows from XP up to 10 , Apple Mac: Mac OS X, 9.0 or Later
Plug and Play
- High-quality key switch
- Low Noise
- Key stroke life time:10,000,000 cycles
- USB connection

Specifications:

Cable Length:	1.5m
Button Life:	10 Million Cycles (MBTF)
Key Travel:	3.5 ± 0.5mm
Operating Force:	55g ± 20g
Supply Voltage:	4.40V ~ 5.20V
Working Current:	<50mA
Storage temp:	-20°C ~ +60°C
Operating Temp:	-5°C ~ +45°C
Storage Humidity:	10% ~ 70% RH
Operating Humidity:	10% ~ 80% RH