

Quick, compact and energy efficient mono laser printers

i-SENSYS
LBP6030

i-SENSYS
LBP6030B

i-SENSYS
LBP6030w

you can



Affordable, compact mono laser printers, ideal for desktop use at home or a small office

An affordable, space saving mono laser printers designed for personal or small office use. Quiet, reliable and highly energy efficient with low power consumption they deliver fast, high quality prints.

Key Features

- Affordable, compact mono laser printer, ideal for personal or small office use
- There's no waiting for documents, thanks to Canon's Quick First-Print technologies plus Fast 18 pages per minute print speed
- High speed USB connectivity
- Save time and money with market leading energy efficiency
- Quiet operation lets you work without distraction
- Recyclable All-in-One print cartridge for maintenance free operation
- Stylish, space saving design that fits virtually anywhere
- Wi-Fi connectivity for easy networking and wireless printing from PCs (LBP6030w)

What's in the Box

Main Unit, Starter Cartridge, Power Cable, Warranty Card & GS Notice sheet, DVD-ROM Getting Started, USB Cable*

Dimensions (W x D x H)

364 mm x 249 mm x 199 mm

Supported OS

Windows Win 8.1(32/64bit)/Win 8(32/64bit)/Win 7(32/64bit)/Win Vista(32/64bit)/XP(32/64bit)/server 2012(32/64bit)/server 2012 R2(64bit)/server 2008(32/64bit)/server 2008 R2(64bit)/ 2003 server(32/64bit)

Mac OS 10.6 to 10.9

Linux (Web distribution)/Citrix(FR2)



PRINT



COPY



FAX



SCAN



Wi-Fi*

Canon

*LBP6030w Only



1 150-sheet tray
2 Cartridge 725



Specifications

PRINTER ENGINE Print speed Printing method Print quality Print resolution Warm-up time First Page Out Time Duty cycle Print margins	18ppm mono (A4) ¹ Monochrome laser beam printing Up to 2400 x 600 dpi with Automatic Image Refinement Up to 600 x 600 dpi Approx. 1 second from Sleep 10 seconds or less from power on Approx. 7.8 seconds or less Max 5,000 pages per month 5 mm-top, bottom, left and right
MEDIA HANDLING Paper input (Standard) Paper output Media types Media sizes Media weights	150-sheet multi-purpose tray 100-sheet face down Plain paper, Heavy Paper, Transparency, Label, Envelope A4/B5/A5/LGL/LTR/EXE/16K/Custom size Env. COM10/Env. Monarch/Env. C5/Env. DL width 76.2 to 216 mm x length 188 to 356 mm Multi-purpose tray: 60 to 163 g/m ²
GENERAL FEATURES Power requirements Power consumption Noise level Dimensions (W x D x H) Weight Operating environment Control panel	AC 220-240V (±10%), 50/60Hz (±2Hz) Maximum: Approx. 870 W or less Active: Average approx. 330 W Standby: Average approx. 1.8 W or less Standby: Average approx. 2.8 W or less (Wi-Fi - LBP6030w) Sleep: Average approx. 0.8 W or less Sleep: Average approx. 1.6 W or less (Wi-Fi - LBP6030w) Typical Electricity Consumption (TEC): 0.47 kWh/week Sound power ² : Active: 6.34 B or less Standby: Inaudible Sound pressure ² : Active: 49.2 dB(A) Standby: Inaudible 364 mm x 249 mm x 199 mm Approx. 5.0 kg Temperature : 10 to 30°C Humidity : 20 to 80%RH (no condensation) 2 LED indicator, 2 operation key - LBP6030 & LBP6030B 3 LED indicator, 3 operation key - LBP6030w

CONTROLLER Memory Printer languages Interface and connectivity Operating systems compatibility	32 MB UFR II LT USB 2.0 Hi-Speed USB 2.0 Hi-Speed & IEEE802.11b/g/n (LBP6030w) Win 8.1(32/64bit)/Win 8(32/64bit)/Win 7(32/64bit)/ Win Vista(32/64bit)/XP(32/64bit)/server 2012(32/64bit)/ server 2012 R2(64bit)/server 2008(32/64bit) / server 2008 R2(64bit)/ 2003 server(32/64bit)/ Mac OS10.6 to 10.9/Linux ³ /Citrix(FR2)
CONSUMABLES All-in-One cartridges	Standard: Cartridge 725 (1,600 pages ⁴) ⁵
Footnote ¹ The print speed may drop depending on the printer driver settings, paper size, paper type and number of pages printed ² Declared noise emission in accordance with ISO 9296 ³ Web distribution only ⁴ Based on ISO/IEC 19752 ⁵ Printer ships with 700 pages starter cartridge Standard disclaimers All specifications subject to change without notice	



Canon Inc.
canon.com

Canon Europe
canon-europe.com

English Edition
© Canon Europa N.V., 2014