

Hole Punch & Die Sets



SLUG-BUSTER® Knockout Punches



- The unique punch profile splits allowing slugs to fall free
- SLUG-BUSTER® punches are available in a range of sizes
- Operation can be by manually turning the Draw Stud with a wrench etc or by using the hydraulic driver

229852

Hole Size	Capacity Mild Steel	Mftrs List No	Order Code	Price Each
12.5 mm (ISO 12)	1.5	06727	358-0751	
15.2 mm (PG 9)	2	31989	358-0763	
16.2mm (ISO 16)	2	35177	358-0775	
18.6 mm (PG 11)	2	31990	358-0787	
20.4mm (ISO 20, PG 13)	2	31991	358-0799	
22.5 mm (PG 16)	2	31962	358-0805	
25.4 mm (ISO 25)	2	35178	358-0817	
28.3 mm (PG 21)	2	31993	358-0829	
30.5 mm	2	36508	358-0830	
32.5 mm (ISO 32)	3	35179	358-0842	
37 mm (PG 29)	3	31995	358-0866	
40.5 mm (ISO40)	3	35180	358-0878	
Spare Bearing Bolts 9.5 x 40mm		00042	358-0921	