



## ERA miGuard IP116

### Wireless WiFi HD IP Camera

#### Summary:

The miGuard IP116 camera is a Wireless WiFi operated IP camera that is compatible with the miGuard range of Alarms. The camera includes a Free App that can be downloaded from the App store or the Google Play store. Via the App, you get to see and hear what's going on in your property from anywhere in the world. The built-in HiFi microphone and speaker allow quality two-way audio communication, and the industrial grade SONY image sensor renders sharp video footage.



#### Features:

- WiFi controlled IP camera
- Super Wide Angle at 5 Megapixels
- Smart control via the Free Smartphone App (iOS and Android)
- HD video quality at 720p
- Crystal clear video even at low light
- Two-Way audio with the built-in microphone and speaker
- Simultaneous viewing by multiple users
- Compatible with the miGuard Wireless Intruder Alarms
- WiFi Quick Link feature, allows quick setup times via the Free App
- Night vision
- 110deg field of vision with a 360deg turning possibilities
- MicroSD card that records in a loop

#### Key Features:

- Quick Link WiFi, set up in minutes
- HD video quality at 720p
- Night Vision
- Expand the memory with the MicroSD slot
- Two-Way Audio Communication with the built-in microphone and speaker
- Free standing or can be mounted to walls or ceilings

#### Kit Includes:

- 1 x IP116 WiFi Camera
- 1 x AC Adapter
- Quick Setup Guide

## Specifications:

<b>Product Name:</b>	<b>HD WiFi Security Alarm Camera</b>
<b>Model No.:</b>	IP116
<b>Image Sensor:</b>	Sony 1/3" CMOS sensor
<b>Min. Illumination: Colour:</b>	0.01 Lux @ (F1.2, AGC ON)
<b>Black and White:</b>	0.001 Lux @ (F1.2, AGC ON)
<b>Shutter Time:</b>	1/50s to 1/100,000s
<b>Lens:</b>	2.4mm F2.0
<b>Angle of View:</b>	110°
<b>Video Compression:</b>	H2.64
<b>Bit Rate:</b>	Self-adaption
<b>Max. Image Resolution:</b>	1280 x 720
<b>Frame Rate:</b>	30fps (1280 x 720)
<b>Storage:</b>	Built-in microSD card slot, up to 32GB
<b>Wireless Standards:</b>	IEEE 802.11b/g/n
<b>Frequency Range:</b>	2.4 GHz ~ 2.4835 GHz
<b>Channel Bandwidth:</b>	20/40 MHz Support
<b>Operation Condition:</b>	Temperature: -30 °C ~ 60 °C Humidity: ≤ 95% (non-condensing)
<b>Power Supply:</b>	DC 5V 2A
<b>Power Consumptions:</b>	5W Max
<b>Size (L x W x H):</b>	91mm x 78mm x 115mm
<b>EAN:</b>	5060215563368
<b>Outer Carton Qty:</b>	20
<b>Outer Carton Dimensions:</b>	56 x 26 x 39
<b>Outer Carton Weight:</b>	12.6kg

## Alarms:



**G5**  
GSM / SMS / RFID  
Wireless Alarm System



**AW1**  
WiFi Wireless Alarm  
System



**A11**  
LCD / PSTN / Touch  
Control Alarm System



**A9**  
Phone Dialler Wireless  
Alarm System



**A105**  
Wireless Apartment /  
Starter Alarm System



**A1R**  
Wireless Outdoor Solar  
Siren Alarm System