

Brand Name: Lenovo
Colour: Black
DisplayPort: Yes
Environmentally Friendly: Yes
Form Factor: Small Form Factor
Graphics Controller: Intel
Manufacturer:
Graphics Controller Model: HD Graphics 530
Graphics Memory Accessibility: Shared
Graphics Memory Technology: DDR4 SDRAM
Green Compliant: Yes
Monitor Included: No
Number of USB 2.0 Ports: 2
Number of USB 3.0 Ports: 4
Operating System Architecture: 64-bit
Operating System Platform: Windows
Operating System: Windows 10 Pro
Optical Drive Type: DVD-Writer
Processor Manufacturer: Intel
Processor Model: i3-6100
Processor Speed: 3.70 GHz
Processor Type: Core i3
Product Family: S510
Product Type: Desktop Computer
Screen Size: No
Standard Memory: 4 GB
Total Number of USB Ports: 6
Total Solid State Drive Capacity: 128 GB
VGA: Yes
Wireless LAN: No

Camera

Screen Size: No

Display & Graphics

Graphics Controller: Intel
Manufacturer:
Graphics Controller Model: HD Graphics 530
Graphics Memory Accessibility: Shared
Graphics Memory Technology: DDR4 SDRAM
Monitor Included: No
Screen Size: No

General Information

Brand Name: Lenovo
Manufacturer Part Number: 10KY005EUK
Manufacturer Website Address: <http://www.lenovo.com/uk/en/>
Manufacturer: Lenovo Group Limited
Package Contents:

- S510 10KY005EUK Desktop Computer
- Keyboard
- Mouse

Product Model: 10KY005EUK
Product Name: S510 10KY005EUK Desktop Computer
Product Series: S510
Product Type: Desktop Computer

Interfaces/Ports

DisplayPort: Yes
Number of USB 2.0 Ports: 2
Number of USB 3.0 Ports: 4
Total Number of USB Ports: 6
VGA: Yes
Wireless LAN: No

Memory

Memory Technology: DDR4 SDRAM
Standard Memory: 4 GB

Miscellaneous

Environmental Certification: ENERGY STAR 6.1
Environmentally Friendly: Yes
Features: Security Slot

Form Factor:	Small Form Factor
Green Compliance Certificate/Authority:	ENERGY STAR 6.1
	ErP Lot 3
	GREENGUARD
	RoHS
Green Compliant:	Yes
Monitor Included:	No
Package Contents:	<ul style="list-style-type: none"> • S510 10KY005EUK Desktop Computer • Keyboard • Mouse

Network & Communication

Wireless LAN: No

Physical Characteristics

Colour: Black
Depth: 320 mm
Form Factor: Small Form Factor
Height: 88.9 mm
Weight (Approximate): 4.13 kg
Width: 294.6 mm

Processor & Chipset

Processor Generation: 6th Gen
Processor Manufacturer: Intel
Processor Model: i3-6100
Processor Speed: 3.70 GHz
Processor Type: Core i3

Product Information

Features: Security Slot
Form Factor: Small Form Factor
Operating System Platform: Windows
Screen Size: No
Width: 294.6 mm

Software

Operating System Architecture: 64-bit
Operating System Platform: Windows
Operating System: Windows 10 Pro

Storage

Features: Security Slot
Optical Drive Type: DVD-Writer
Optical Media Supported: DVD-RAM/±R/±RW
Total Solid State Drive Capacity: 128 GB

Technical Information

Features: Security Slot
Memory Technology: DDR4 SDRAM
Operating System: Windows 10 Pro
Optical Drive Type: DVD-Writer
Optical Media Supported: DVD-RAM/±R/±RW
Processor Generation: 6th Gen
Processor Manufacturer: Intel
Screen Size: No
Wireless LAN: No

Video

Graphics Controller: Intel
Manufacturer:
Graphics Controller Model: HD Graphics 530
Graphics Memory Accessibility: Shared
Graphics Memory Technology: DDR4 SDRAM

Warranty

Limited Warranty: 1 Year

Wireless Specifications

Features: Security Slot
Wireless LAN: No