

7000D Series
DURA SERIES



AVAILABLE
COLORS



BLACK

DIMENSIONS

SEAT

19 1/4" W x 17 1/4" D
1 1/2" Thick

BACK

15 1/2" W x 14 1/2" H
1" Thick

BUILT TO ORDER

Each chair is configured to your exact specifications – choice of arms, tilt, height range, base style, and glides/caster options.

FEATURED MODEL

7301D with AA arms and 3850S/5 casters



Height Range	Base Style	Seat Height Adjustment	Adjustment Mechanism	Footring	Standard Model #	Cleanroom Class 10/ ISO4 Model #
DESK	23" Black Nylon	15" – 20"	2 Way	-	7000D	7000DC
			3 Way	-	7001D	7001DC
			4 Way	-	7002D	7002DC
	25" Polished Aluminum	14 ½" – 19 ½"	2 Way	-	7050D	7050DC
			3 Way	-	7051D	7051DC
			4 Way	-	7052D	7052DC
MID	27" Black Nylon	19" – 26 ½"	2 Way	18" Adj. Chrome	7300D	7300DC
			3 Way	18" Adj. Chrome	7301D	7301DC
			4 Way	18" Adj. Chrome	7302D	7302DC
	27" Polished Aluminum	18 ½" – 26"	2 Way	18" Adj. Chrome	7350D	7350DC
			3 Way	18" Adj. Chrome	7351D	7351DC
			4 Way	18" Adj. Chrome	7352D	7352DC
	22" Black Tubular Steel	19" – 24'	2 Way	19" Welded Chrome	7200D	-
			3 Way	19" Welded Chrome	7201D	-
			4 Way	19" Welded Chrome	7202D	-
	22" Chrome Tubular Steel	19" – 24'	2 Way	19" Welded Chrome	-	7210DC
			3 Way	19" Welded Chrome	-	7211DC
			4 Way	19" Welded Chrome	-	7212DC
TALL	27" Black Nylon	21" – 31"	2 Way	18" Adj. Chrome	7500D	7500DC
			3 Way	18" Adj. Chrome	7501D	7501DC
			4 Way	18" Adj. Chrome	7502D	7502DC
	27" Polished Aluminum	20 ½" – 30 ½"	2 Way	18" Adj. Chrome	7550D	7550DC
			3 Way	18" Adj. Chrome	7551D	7551DC
			4 Way	18" Adj. Chrome	7552D	7552DC
	22" Black Tubular Steel	24" – 29"	2 Way	19" Welded Chrome	7600D	-
			3 Way	19" Welded Chrome	7601D	-
			4 Way	19" Welded Chrome	7602D	-
	22" Chrome Tubular Steel	24" – 29"	2 Way	19" Welded Chrome	-	7610DC
			3 Way	19" Welded Chrome	-	7611DC
			4 Way	19" Welded Chrome	-	7612DC



FEATURED MODEL
7351D with AA arms
and 3850S/5 casters

ACCESSORIES

ARMS



AA

Standard and CR Models
Tilt models only, must be ordered with chair.

CASTERS

Casters add 1" to seat height range.



HARD FLOOR CASTERS

Standard: 3850S/5
Tubular base: CADS/5



CARPET CASTERS

Standard: 3850/5
Tubular base: CAD/5



SPECIALTY CASTERS

INTERVAL BRAKING
Standard: IBCS
REVERSE BRAKING
Standard: RBCS