

3000 Series
VERSA SERIES



DIMENSIONS

POLYURETHANE SEAT
14" diameter
2" seat thickness


VINYL OR FABRIC SEAT
16" diameter
Seat foam density:
2 ½lb, 55 IFD
2 ¾" seat thickness

UPHOLSTERY OPTIONS

STANDARD



ESD



BUILT TO ORDER

Each chair is configured to your exact specifications – upholstery, height range, base style, and glides/caster options.



Height Range	Base Style	Seat Height Adjustment	Seat Type	Standard Model #	ESD Model #	Cleanroom Class 10/ ISO4 Model #
DESK	23" Black Nylon	15" – 20"	Polyurethane	3000P	-	-
		16" – 21"	Fabric	3000F	-	-
		16" – 21"	Vinyl	3000V	-	-
	25" Polished Aluminum	14 ½" – 19 ½"	Polyurethane	3050P	-	3050C1P
		15 ½" – 20 ½"	Fabric	3050F	3050E-F	-
		15 ½" – 20 ½"	Vinyl	3050V	3050E-V	-
MID	27" Black Nylon	18 ½" – 26"	Polyurethane	3300P	-	-
		19 ½" – 27"	Fabric	3300F	-	-
		19 ½" – 27"	Vinyl	3300V	-	-
	27" Polished Aluminum	17 ½" – 25"	Polyurethane	3350P	-	3350C1P
		18 ½" – 26"	Fabric	3350F	3350E-F	-
		18 ½" – 26"	Vinyl	3350V	3350E-V	-
	22" Black Tubular Steel	18" – 23"	Polyurethane	3200P	-	-
		19" – 24"	Fabric	3200F	-	-
		19" – 24"	Vinyl	3200V	-	-
	22" Chrome Tubular Steel	18" – 23"	Polyurethane	3210P	-	3210C1P
		19" – 24"	Fabric	3210F	3210E-F	-
		19" – 24"	Vinyl	3210V	3210E-V	-
TALL	27" Black Nylon	22" – 32"	Polyurethane	3500P	-	-
		23" – 33"	Fabric	3500F	-	-
		23" – 33"	Vinyl	3500V	-	-
	27" Polished Aluminum	20 ½" – 30 ½"	Polyurethane	3550P	-	3550C1P
		21 ½" – 31 ½"	Fabric	3550F	3550E-F	-
		21 ½" – 31 ½"	Vinyl	3550V	3550E-V	-
	22" Black Tubular Steel	23" – 28"	Polyurethane	3600P	-	-
		24" – 29"	Fabric	3600F	-	-
		24" – 29"	Vinyl	3600V	-	-
22" Chrome Tubular Steel	23" – 28"	Polyurethane	3610P	-	3610C1P	
	24" – 29"	Fabric	3610F	3610E-F	-	
	24" – 29"	Vinyl	3610V	3610E-V	-	



FEATURED MODEL
3600F with
CADS/5 casters

ACCESSORIES

FOOTRING



STANDARD: ACF-18
ESD: ACF-18E

Recommended for stools with a seat height range above 19".

CASTERS

Casters add 1" to seat height range.



HARD FLOOR CASTERS

Standard:
5-star: 3850S/5
Tubular: CADS/5
ESD: CARD5S



CARPET CASTERS

Standard:
5-star: 3850/5
Tubular: CAD/5
ESD: CAPD5S



SPECIALTY CASTERS

INTERVAL BRAKING
Standard: IBCS
ESD: IBCS-ESD
REVERSE BRAKING
Standard: RBCS
ESD: RBCS-ESD