

CLIFF

MAINS INLET SOCKETS




CL19191 - MS1X/S1 SNAP-IN, UP TO 1.1mm PANEL, 0.5mm THK SOLDER TAGS

CL19192 - MS1X/S SNAP-IN, UP TO 2.1mm PANEL, 0.5mm THK SOLDER TAGS




CL19193 - MS1X/A1 SNAP IN, UP TO 1.1mm PANEL, 1/4" FASTONS




CL191930 - MS1X/A1 SNAP IN, 2 POLE, UP TO 1.1mm PANEL, 1/4" FASTONS




CL19192RB - MS1/X SNAP-IN, 1.5mm PANEL, 6.3mm FASTONS



CL19268 - FUSED MAINS INLET SOCKET XMS3, 1/4" FASTONS (4 TAGS), SELFTAP SCREWS



CL1927RB - FUSED MAINS INLET SOCKET MS3, 4.8mm FASTONS (3 TAGS) WITH CAPTIVE FUSEHOLDER



CL19274 - FUSE CARRIER FOR MS3 230V/115V