

350mA Constant Current LED Driver 3vdc-12vdc



Features

Universal Input 100-240vac


Terminal Screw for Input / Output connection

IP20 Indoor use (dry location) only

Short circuit and over heat protection

Forward voltage range 3vdc to 12vdc

| | |
|-----------------------------|-----------------------------|
| Part Numbers | PLC3512-01 |
| Inrush Current | 20A max. |
| DC Voltage range | 3vdc to 12vdc |
| Rated Output Current | 350mA +/-6% |
| Efficiency | 60% |
| Over Load Protection | 100-135% rated output power |
| Safety | EN61347 / EN55015 |
| Case Size | Refer to drawing |



Full specification documents on each part included in this data sheet are available on request from PowerPax UK Ltd. PowerPax accepts no responsibility for typographical errors in the production of this leaflet. Product specifications are subject to change without notice