

Ladder Ties

PRO-POWER
Quality Cables



Stainless steel 316 cable ties, supplied either coated or uncoated. The coated cable ties have an electrostatically applied black epoxy finish, making them extremely resistant to corrosion. The construction of these ties gives them greater flexibility than the standard type.

- Self-locking for easy application
- Supplied in packs of 100

Operating temperature -80°C to +538°C Uncoated

Operating temperature -80°C to +150°C Coated

| | | Min. Tensile | Max. | Uncoated | Coated |
|--------|-------|---------------|-------------|--------------------------|--------------------------|
| Length | Width | Strength (kg) | Bundle Dia. | Order Code | Order Code |
| 100 | 7 | 44.5 | | 981-3675 | 981-3829 |
| 200 | 7 | 44.5 | 50 | 981-3683 | 981-3837 |
| 225 | 7 | 44.5 | 60 | 981-3691 | 981-3845 |
| 300 | 7 | 44.5 | 80 | 981-3705 | 981-3853 |
| 360 | 7 | 44.5 | 105 | 981-3713 | 981-3861 |
| 450 | 7 | 44.5 | 115 | 981-3721 | 981-3870 |
| 610 | 7 | 44.5 | 150 | 981-3730 | 981-3888 |
| 750 | 7 | 44.5 | 200 | 981-3748 | 981-3896 |
| 150 | 12 | 113.6 | | 981-3756 | 981-3900 |
| 225 | 12 | 113.6 | 60 | 981-3764 | 981-3918 |
| 300 | 12 | 113.6 | 80 | 981-3772 | 981-3926 |
| 360 | 12 | 113.6 | 105 | 981-3780 | 981-3934 |
| 450 | 12 | 113.6 | 115 | 981-3799 | 981-3942 |
| 610 | 12 | 113.6 | 150 | 981-3802 | 981-3950 |
| 750 | 12 | 113.6 | 200 | 981-3810 | 981-3969 |

100 Per Pack