


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0430300003**
Status: **Active**
Overview: Micro-Fit 3.0™ Connectors
Description: Micro-Fit 3.0™ Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 20-24 AWG, Reel

Documents:

| | |
|--|--|
| 3D Model | Packaging Specification PK-43030-001 (PDF) |
| Drawing (PDF) | RoHS Certificate of Compliance (PDF) |
| Product Specification PS-43045 (PDF) | Product Literature (PDF) |
| Product Specification TS-43045-002-001 (PDF) | |



General

| | |
|-----------------------------|---|
| Product Family | Crimp Terminals |
| Series | 43030 |
| Application | Power |
| Crimp Quality Equipment | Yes |
| Overview | Micro-Fit 3.0™ Connectors |
| Packaging Alternative | 43030-0009 (Loose) |
| Product Literature Order No | 987650-5984 |
| Product Name | Micro-Fit 3.0™ |
| UPC | 800754369169 |

Physical

| | |
|--------------------------------|----------------------|
| Gender | Female |
| Material - Metal | Phosphor Bronze |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Tin |
| Net Weight | 0.062/g |
| Packaging Type | Reel |
| Plating min - Mating | 0.762µm |
| Plating min - Termination | 2.540µm |
| Termination Interface: Style | Crimp or Compression |
| Wire Insulation Diameter | 1.85mm max. |
| Wire Size AWG | 20, 22, 24 |
| Wire Size mm² | N/A |

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 5.0A |
|-------------------------------|------|

Solder Process Data

| | |
|------------------------------|-----|
| Lead-free Process Capability | N/A |
|------------------------------|-----|

Material Info

Reference - Drawing Numbers

| | |
|-------------------------|----------------------------|
| Packaging Specification | PK-43030-001 |
| Product Specification | PS-43045, TS-43045-002-001 |
| Sales Drawing | SD-43030-**** |

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[43030 Series](#)

Use With

[43025](#) , [43645](#) Micro-Fit 3.0™ Receptacle Housings, [44133](#) Micro-Fit BMI™ Panel Mount Receptacle Housings

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

FineAdjust™
Applicator for
Insulation OD

Product #

[0639018800](#)

| | |
|---|--|
| 1.10-1.30mm - 20-24 AWG FineAdjust™ Applicator for Insulation OD 0.91-1.09mm - 20-24 AWG FineAdjust™ Applicator for Insulation OD 1.30-1.85mm, 20-24 AWG Wire T2 Terminator™ for insulation OD 0.91-1.09mm - 20-24 AWG T2 Terminator™ for insulation OD 1.30-1.85mm - 20-24 AWG T2 Terminator™ for insulation OD 1.10-1.30mm - 20-24 AWG Hand Crimp Tool Extraction Tool Insertion Tool for Crimp Terminal | <u>0639018900</u> <u>0639004500</u> <u>0639118900</u> <u>0639104500</u> <u>0639118800</u> <u>0638190000</u> <u>0011030043</u> <u>0638120800</u> |
| Japan | |
| Description | Product # |
| Applicator for M21 1A Bench Press, 20-30 AWG Wire | <u>0572983000</u> |

This document was generated on 11/23/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION