

## Ground distribution module **EB-GND8**



### Advantages

0 V collective terminal with 4 or 8 inputs

EB-GND4: Output to feed back up to 40 A to the power supply provided

Total current up to 40 A per module

### Applications

Ground distribution module to feed back the 0 V signal to the power supply as a replacement for the series terminal.

### Approvals



## Ground distribution module EB-GND8

Electrical data	
Type	EB-GND8
Input	
Input rated voltage	12/24/48 Vdc
Input rated current	8 x 10 A
Output	
Output current	max. 40 A
Environment	
Ambient temperature	-40 °C to +70 °C
Storage temperature	-40 °C to +85 °C
Accessory	
Cross connection	EB-BAR41 for bridging modules in series
Order numbers	
Order Number	EB-GND8

Mechanical data	
Type	EB-GND8
Terminal and mounting	
Terminals input, (spring clamp terminal)	0,08 - 2,5 mm <sup>2</sup>
Terminals output, (spring clamp terminal)	-
Mounting position	horizontal for standard rail DIN TH 35
Measures and weights	
Dimension (W x H x D)	12 x 99 x 60 mm
Weight	0,040 kg

