


T 227



Euromas
Enclosure, ABS
Order no.: 03227000

Colour of enclosure group	Light grey, similar to RAL 7035; special colours on request
Protection class	Depending on the model: IP 65 or IP 66/DIN EN 60529; IP 67 available on request for some sizes.
Enclosure material	ABS, PC (UV stabilised) and selected sizes in PC UL 94 V0 (additional UL 94 V0 versions on request), seal made of CR; for details see Technical Information
Scope of delivery	Scope of delivery: Lid and base, lid screws made of V2A, self-tapping screws for mounting bosses Note: SV = version with quick-release fastener. IP = Ingress protection acc. to DIN EN 60529



A	122 mm
B	120 mm
C	85 mm
a1	115 mm
a2	96,2 mm
b1	113 mm
b2	76,2 mm
c1	15 mm
c2	78 mm

Technical drawings	Catalogue drawing in DXF format: 03227000_T-227.dxf (676 KB) 3D product data in STEP format: Registration necessary Basic drawing for processing work: 03227000_T-227-G.dxf (362 KB) Catalogue drawing in PDF format: 03227000_T-227.pdf (90 KB)
Chapter download	Euromas_ABS_PC_GB.pdf (338 KB)

Accessories



Mounting plates, laminated paper (Pertinax), galvanised steel for version 260

22000500 [M](#) For EM/ET 217, EM/ET 227, M/T 217, M/T 227-228



Knurled screws

22003100 [RD](#) For M/T 210-215, M/T 217, M/T 220-227, M/T 231



Rubber feet, plug-in

22003300 [E](#) For M/T 208-260



Silicone seal for lid

22003700 [SIL](#) For M/T 217, M/T 227-228



Wall brackets on rear, screw-on, polycarbonate

22004900 [WL](#) For M/T 210-243, M/T 246-253



DIN rails DIN EN 60715 TH 15, galvanised steel

22001900 [TS 15](#) For M/T 215-217, M/T 226-230



DIN rails DIN EN 60715 TH 35, galvanised steel

22001910 [TS 35](#)

For M/T 215-217, M/T 226-230



Threaded inserts for mounting bosses

59002810 [DODGE](#)

ND = 4.0 x 6.5

[M3x6,5](#)

59002820 [DODGE](#)

ND = 5.4 x 9.5

[M4x9,5](#)

* = Available on request