

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0547220164**  
**Status:** **Active**  
**Overview:** SlimStack™ 0.50mm Pitch Board-to-Board Connectors  
**Description:** 0.50mm Pitch SlimStack™ Receptacle, Surface Mount, Dual Row, Vertical, 1.50mm Stacking Height, Lower Circuit Size Version, 16 Circuits, Gold (Au) Plating with Nickel (Ni) Barrier Plating Between Contact and Tail

**Documents:**

[3D Model](#) [Application Specification 547220000-A00 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-54722-010-001 \(PDF\)](#)

**Agency Certification**

UL E29179

**General**

Product Family PCB Receptacles  
Series [54722](#)  
Application Board-to-Board, Signal  
Comments Embossed Tape Reel Height: 380.00mm|Gold plating with Nickel plating between contact and tail  
Overview [SlimStack™ 0.50mm Pitch Board-to-Board Connectors](#)  
Product Name SlimStack™  
UPC 756054574317

**Physical**

Circuits (Loaded) 16  
Circuits (maximum) 16  
Color - Resin Black  
Durability (mating cycles max) 30  
Glow-Wire Compliant No  
Lock to Mating Part None  
Mated Height 1.50mm  
Material - Metal Phosphor Bronze  
Material - Plating Mating Gold  
Material - Plating Termination Gold  
Material - Resin High Temperature Thermoplastic  
Net Weight 59.641/mg  
Number of Rows 2  
Orientation Vertical  
PCB Locator No  
PCB Retention None  
PCB Thickness - Recommended 1.60mm  
Packaging Type Embossed Tape on Reel  
Pitch - Mating Interface 0.50mm  
Polarized to PCB No  
Surface Mount Compatible (SMC) N/A  
Temperature Range - Operating -40°C to +105°C  
Termination Interface: Style Surface Mount


**Electrical**

Current - Maximum per Contact 0.5A  
Voltage - Maximum 50V

**Material Info**

**Reference - Drawing Numbers**

Application Specification 547220000-A00



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/21/2016 (20 June 2016)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[54722](#) Series

**Mates With**

[55560](#) PCB Header

This document was generated on 11/18/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**