

Length	Order Code	price each	
		1+	5+
<b>Blue</b>			
2m	<b>CS17333</b>	<b>1.49</b>	<b>1.32</b>
3m	<b>CS17334</b>	<b>1.95</b>	<b>1.74</b>
5m	<b>CS17335</b>	<b>2.91</b>	<b>2.67</b>
10m	<b>CS17336</b>	<b>4.43</b>	<b>4.12</b>
15m	<b>CS23725</b>	<b>5.82</b>	<b>5.28</b>
20m	<b>CS23726</b>	<b>7.72</b>	<b>7.04</b>

 **FastCAT5e Snagless STP Patch Leads**



- RJ45 Fast Cat5e STP patch cables
- Ideal for use with 10 and 100 Base-T networks
- Premium snagless-type moulding protects connectors from damage during installation
- 50 Micron gold-plated connectors to ensure a clean and clear transmission
- Exceeds performance requirements of Category 5e
- PowerSum tested
- Belkin lifetime warranty

645609

Description	Order Code	price each	
		1+	5+
<b>Black</b>			
1m	<b>CS22047</b>	<b>3.15</b>	<b>2.92</b>
2m	<b>CS22048</b>	<b>4.08</b>	<b>3.77</b>
5m	<b>CS22049</b>	<b>5.62</b>	<b>5.19</b>
10m	<b>CS22050</b>	<b>9.42</b>	<b>8.78</b>
15m	<b>CS22051</b>	<b>12.86</b>	<b>11.88</b>
<b>Grey</b>			
1m	<b>CS22052</b>	<b>3.15</b>	<b>2.92</b>
2m	<b>CS22053</b>	<b>4.08</b>	<b>3.77</b>
5m	<b>CS22054</b>	<b>5.62</b>	<b>5.19</b>
10m	<b>CS22055</b>	<b>9.42</b>	<b>8.78</b>
15m	<b>CS22056</b>	<b>12.86</b>	<b>11.88</b>
<b>Blue</b>			
1m	<b>CS22057</b>	<b>3.15</b>	<b>2.92</b>
2m	<b>CS22058</b>	<b>4.08</b>	<b>3.77</b>

Description	Order Code	price each	
		1+	5+
<b>Grey</b>			
0.5m	<b>CS17315</b>	<b>0.78</b>	<b>0.67</b>
1m	<b>CS17316</b>	<b>1.17</b>	<b>1.00</b>
2m	<b>CS17317</b>	<b>1.85</b>	<b>1.52</b>
3m	<b>CS17318</b>	<b>2.37</b>	<b>2.06</b>
5m	<b>CS17319</b>	<b>2.84</b>	<b>2.57</b>
10m	<b>CS17320</b>	<b>3.92</b>	<b>3.65</b>
15m	<b>CS17321</b>	<b>4.85</b>	<b>4.54</b>
20m	<b>CS17322</b>	<b>5.98</b>	<b>5.64</b>
25m	<b>CS17323</b>	<b>7.54</b>	<b>6.95</b>
30m	<b>CS17324</b>	<b>9.42</b>	<b>8.64</b>

<b>Blue</b>			
0.5m	<b>CS22804</b>	<b>0.78</b>	<b>0.67</b>
1m	<b>CS22805</b>	<b>1.17</b>	<b>1.00</b>
2m	<b>CS22806</b>	<b>1.85</b>	<b>1.52</b>
3m	<b>CS22807</b>	<b>2.37</b>	<b>2.06</b>
5m	<b>CS22808</b>	<b>2.84</b>	<b>2.57</b>
10m	<b>CS22809</b>	<b>3.92</b>	<b>3.65</b>
20m	<b>CS22810</b>	<b>5.98</b>	<b>5.64</b>

<b>Violet</b>			
0.5m	<b>CS22811</b>	<b>0.78</b>	<b>0.67</b>
1m	<b>CS22812</b>	<b>1.17</b>	<b>1.00</b>
2m	<b>CS22813</b>	<b>1.85</b>	<b>1.52</b>
3m	<b>CS22814</b>	<b>2.37</b>	<b>2.06</b>
5m	<b>CS22815</b>	<b>2.84</b>	<b>2.57</b>
10m	<b>CS22816</b>	<b>3.92</b>	<b>3.65</b>
20m	<b>CS22817</b>	<b>5.98</b>	<b>5.64</b>

<b>Yellow</b>			
0.5m	<b>CS22818</b>	<b>0.78</b>	<b>0.67</b>
1m	<b>CS22819</b>	<b>1.17</b>	<b>1.00</b>
2m	<b>CS22820</b>	<b>1.85</b>	<b>1.52</b>
3m	<b>CS22821</b>	<b>2.37</b>	<b>2.06</b>
5m	<b>CS22822</b>	<b>2.84</b>	<b>2.57</b>
10m	<b>CS22823</b>	<b>3.92</b>	<b>3.65</b>
20m	<b>CS22824</b>	<b>5.98</b>	<b>5.64</b>

 **CAT 5e UTP Crossover Cable**



Length	Order Code	price each	
		1+	10+
0.5m	<b>CS26198</b>	<b>2.85</b>	<b>2.66</b>
1m	<b>CS26199</b>	<b>2.94</b>	<b>2.74</b>
2m	<b>CS26200</b>	<b>3.28</b>	<b>3.05</b>
3m	<b>CS26201</b>	<b>3.49</b>	<b>3.24</b>
5m	<b>CS26202</b>	<b>4.67</b>	<b>4.37</b>
10m	<b>CS26203</b>	<b>6.84</b>	<b>6.36</b>



**LSOH Cat6 UTP Extension Leads**



- Cat6 plug to socket extension cables
- Quick and flexible solution to extend Cat6 cable runs
- Low Smoke Zero Halogen PVC construction
- Wired straight through (1-1)
- Various colours available

656561

Length	Order Code	price each	
		1+	3+
<b>Grey</b>			
3m	<b>CS23069</b>	<b>5.66</b>	<b>5.24</b>
5m	<b>CS23070</b>	<b>6.43</b>	<b>6.18</b>
10m	<b>CS23071</b>	<b>8.96</b>	<b>8.52</b>
<b>Black</b>			
3m	<b>CS23073</b>	<b>5.66</b>	<b>5.24</b>
20m	<b>CS23076</b>	<b>16.79</b>	<b>15.85</b>
<b>Green</b>			
5m	<b>CS23078</b>	<b>6.43</b>	<b>6.18</b>
10m	<b>CS23079</b>	<b>8.96</b>	<b>8.52</b>
20m	<b>CS23080</b>	<b>16.79</b>	<b>15.85</b>
<b>Blue</b>			
5m	<b>CS23082</b>	<b>6.43</b>	<b>6.18</b>
10m	<b>CS23083</b>	<b>8.96</b>	<b>8.52</b>
<b>Red</b>			
5m	<b>CS23086</b>	<b>6.43</b>	<b>6.18</b>
10m	<b>CS23087</b>	<b>8.96</b>	<b>8.52</b>

5m	<b>CS22059</b>	<b>5.62</b>	<b>5.19</b>
10m	<b>CS22060</b>	<b>9.42</b>	<b>8.78</b>
15m	<b>CS22061</b>	<b>12.86</b>	<b>11.88</b>
<b>Green</b>			
10m	<b>CS22065</b>	<b>9.42</b>	<b>8.78</b>
<b>Red</b>			
1m	<b>CS22067</b>	<b>3.15</b>	<b>2.92</b>
2m	<b>CS22068</b>	<b>4.08</b>	<b>3.77</b>
5m	<b>CS22069</b>	<b>5.62</b>	<b>5.19</b>
10m	<b>CS22070</b>	<b>9.42</b>	<b>8.78</b>
15m	<b>CS22071</b>	<b>12.86</b>	<b>11.88</b>
<b>White</b>			
1m	<b>CS22072</b>	<b>3.15</b>	<b>2.92</b>
2m	<b>CS22073</b>	<b>4.08</b>	<b>3.77</b>
5m	<b>CS22074</b>	<b>5.62</b>	<b>5.19</b>
10m	<b>CS22075</b>	<b>9.42</b>	<b>8.78</b>
15m	<b>CS22076</b>	<b>12.86</b>	<b>11.88</b>

**pro-SIGNAL CAT5E Crossover Cable**



- UTP CAT5E crossover cables
- RJ45 connectors
- Easily identified as crossover cable due to black connector boots

650201



- For 10 and 100 Base-T networks
- 50 micron gold plated connectors for clean and clear transmission
- Molded strain relief provides extra security around connector
- Lifetime warranty

429175

Length	Order Code	price each	
		1+	5+
1m	<b>CS12218</b>	<b>3.20</b>	<b>2.84</b>
2m	<b>CS12219</b>	<b>3.89</b>	<b>3.52</b>
3m	<b>CS12220</b>	<b>4.24</b>	<b>3.78</b>
5m	<b>CS12221</b>	<b>5.86</b>	<b>5.18</b>
10m	<b>CS12222</b>	<b>7.57</b>	<b>6.96</b>

**pro-SIGNAL CAT 6 Extension Leads**



- CAT 6 plug to socket extension cables
- Fully tested UTP cables
- Wired straight 1-1

705106

20m	<b>CS23088</b>	<b>16.79</b>	<b>15.85</b>
-----	----------------	--------------	--------------

**pro-SIGNAL**

**CAT 6 RJ45 Patch Cables**



- RJ45 to RJ45 UTP, Cat 6 patch cables
- Selection of colours and lengths available

537352

Description	Order Code	price each	
		1+	5+
<b>Grey</b>			
0.2m	<b>CS17560</b>	<b>1.39</b>	<b>1.17</b>
0.5m	<b>CS17235</b>	<b>1.77</b>	<b>1.53</b>
1m	<b>CS17236</b>	<b>2.29</b>	<b>1.95</b>
2m	<b>CS17237</b>	<b>2.75</b>	<b>2.42</b>
3m	<b>CS17238</b>	<b>3.15</b>	<b>2.72</b>
5m	<b>CS17239</b>	<b>4.24</b>	<b>3.45</b>
10m	<b>CS17240</b>	<b>7.11</b>	<b>6.31</b>
15m	<b>CS17241</b>	<b>8.35</b>	<b>7.25</b>
20m	<b>CS17242</b>	<b>9.62</b>	<b>8.53</b>
25m	<b>CS17243</b>	<b>10.81</b>	<b>9.87</b>
30m	<b>CS17244</b>	<b>12.75</b>	<b>11.46</b>
<b>Red</b>			
0.2m	<b>CS17561</b>	<b>1.39</b>	<b>1.17</b>

Cables and Adaptors

All Prices Exclude VAT

**Order Now**

**cpc.co.uk**

**08447 88 00 88**

**1017**