



Accessories for Wireless products

RF magnet antenna 5db R-SMA plug-in connector straight 3.6 m

Material number: 1188987 (Material number old: 90598014)

Features/Options

- RF magnet antenna with straight R-SMA plug-in connector without ferrite core
- Suitable for SW915
- Cable length 3.6 m
- Ordering unit: 1 piece

Product image



Technical data

Frequency	824 - 960 MHz, 1.8 GHz / 1.9 GHz
Type	Magnet foot antenna
Impedance	50 Ohm
Gain	5 dB
Colour	black
Dimensions	Ø foot 77 mm, height approx. 660 mm
Cable	3.6 m RG58
Connector	R-SMA (male)
Weight	388 g

Errors and omissions excepted.

Arrangement of receiver and switch antenna



Optimum
mounting

Possible
mounting

Unsuitable
mounting

Note

Magnetic base antennae must be mounted on a metal plate of min. 250 x 250 mm size.