


Part Number: 192DX00X

Type	Size	Rating	Description
LED	M12	-	LED Prominent Panel Indicator

Dimensions (mm)



Part #	Colour	Voltage V <sub>f</sub>	Intensity (mcd@20mA)
192DX000	Red	2.0	100
192DX001	Green	2.2	60
192DX002	Yellow	2.1	50

Bezel types - X=0 satin chrome / X=1 black chrome / X=2 matt chrome

Notes:

- 1 Electrical & optical data are measured at an ambient temperature of 25°C
- 2 Luminous intensity at DC
- 3 Storage temperature -25 °C to +80°C
- 4 Application temperature -20 °C to +60°C
- 5 Due to component tolerances, colour temperature variations may be observed
- 6 Sealed to IP67 above panel when supplied gasket used
- 7 The plastic(polycarbonate) has limited chemical resistance
- 8 RoHS & REACH SVHC compliant