



CorePro LEDcapsule MV

CorePro LEDcapsule MV

CorePro LEDcapsuleMV 2.5-25W 827 G9

This single-ended mains-voltage capsule for G9-base luminaires delivers directional light, making it a true alternative to halogen capsule lamps. It is particularly suitable for task lighting in shops, hotels and restaurants, and ideal for desk lamps and cabinet lighting. Compatible with existing fixtures with G9 holders and designed for retrofit replacement of halogen capsules, CorePro LEDcapsule delivers huge energy savings and minimizes maintenance costs, without any compromise on light quality.

Product data

General Information	
Cap base	G9 [G9]
Bulb shape	- [-]
Nominal lifetime (nom.)	15000 h
Switching cycle	50000X
Technical type	2.5-25W
Light Technical	
Luminous flux (nom.)	204 lm
Luminous flux (rated) (nom.)	204 lm
Colour designation	Warm white (WW)
Correlated colour temperature (nom.)	2700 K
Luminous efficacy (rated) (nom.)	81.6 lm/W
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 Hz
Power (Rated) (Nom)	2.5 W
Lamp current (nom.)	29 mA
Wattage equivalent	25 W
Starting time (nom.)	0.5 s
Power factor (nom.)	0.4
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	no
Approval and Application	
Energy efficiency label (EEL)	A+
Energy Consumption kWh/1000 h	3 kWh

CorePro LEDcapsule MV


CorePro LEDcapsule MV

Product Data

Full product code	871869641920500
Order product name	CorePro LEDcapsuleMV 2.5-25W 827 G9
EAN/UPC – product	8718696419205
Order code	41920500
Local Code	LED2WG927

Numerator – quantity per pack	1
Numerator – packs per outer box	12
Material no. (12NC)	929001133402
Net weight (piece)	0.012 kg

Dimensional drawing



LED 2.5-25W 827 G9

Product	D	C
CorePro LEDcapsuleMV 2.5-25W 827 G9	18 mm	53 mm

