



# CorePro LEDcapsule MV

## CorePro LEDcapsuleMV 2.3-25W G9 827 D

This single-ended mains-voltage capsule for G9-base luminaires delivers directional light, making it a true alternative to halogen capsule lamps. It is particularly suitable for task lighting in shops, hotels and restaurants, and ideal for desk lamps and cabinet lighting. Compatible with existing fixtures with G9 holders and designed for retrofit replacement of halogen capsules, CorePro LEDcapsule delivers huge energy savings and minimizes maintenance costs, without any compromise on light quality.

### Product data


General Information		Wattage equivalent	
Cap base	G9 [ G9]		25 W
Nominal lifetime (nom.)	15000 h	Starting time (nom.)	0.5 s
Switching cycle	50000X	Warm-up time to 60% light (nom.)	0.5 s
Technical type	2.3-25W	Power factor (nom.)	0.7
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Luminous flux (nom.)	215 lm	T-Case maximum (nom.)	82 °C
Luminous flux (rated) (nom.)	215 lm		
Colour designation	Warm white (WW)	Controls and Dimming	
Correlated colour temperature (nom.)	2700 K	Dimmable	Yes
Luminous efficacy (rated) (nom.)	93.48 lm/W		
Colour consistency	<6	Approval and Application	
Color rendering index (nom.)	80	Energy-saving product	Yes
LLMF at end of nominal lifetime (nom.)	70 %	Suitable for accent lighting	No
		Energy efficiency label (EEL)	A++
		Energy Consumption kWh/1000 h	3 kWh
Operating and Electrical		Product Data	
Input frequency	50-60 Hz	Full product code	871869657869800
Power (Rated) (Nom)	2.3 W		
Lamp current (nom.)	15 mA		

# CorePro LEDcapsule MV

Order product name	CorePro LEDcapsuleMV 2.3-25W G9 827 D
EAN/UPC – product	8718696578698
Order code	57869800
Numerator – quantity per pack	1
Numerator – packs per outer box	12

Material no. (12NC)	929001232002
Net weight (piece)	0.012 kg

## Dimensional drawing



Product	D	C
CorePro LEDcapsuleMV 2.3-25W G9 827 D	23 mm	51 mm

Capsule 230V 2.3W-25W 210lm 2700K G9 D

Photometric data

General Uniform Lighting

