



# CorePro LEDlinear MV

## CorePro LED linear R7S 118mm 6.5-60W 830


CorePro R7S is a retrofit replacement for traditional double-ended linear R7S lamps. Its 'light all around' design delivers light that is just like a halogen lamp. The deep dimming function enables a cosy ambience when using a dimmable fixture.

### Product data

General Information		Voltage (Nom)	
Cap base	R7S [ R7s]	220-240 V	
Nominal lifetime (nom.)	20000 h	Controls and Dimming	
Switching cycle	50000X	Dimmable	no
Technical type	6.5-60W	Mechanical and Housing	
Light Technical		Bulb finish	Clear (CL)
Beam Angle (Nom)	300 °	Approval and Application	
Light distribution	- [-]	Energy efficiency label (EEL)	A++
Luminous flux (nom.)	806 lm	Energy Consumption kWh/1000 h	7 kWh
Luminous flux (rated) (nom.)	806 lm	Product Data	
Colour designation	White (WH)	Full product code	871869652253000
Rated beam angle	300 °	Order product name	CorePro LED linear R7S 118mm 6.5-60W 830
Correlated colour temperature (nom.)	3000 K	EAN/UPC – product	8718696522530
Color rendering index (nom.)	80	Order code	52253000
Operating and Electrical		Numerator – quantity per pack	1
Input frequency	50-60 Hz	Numerator – packs per outer box	10
Power (Rated) (Nom)	6.5 W	Material no. (12NC)	929001186102
Lamp current (nom.)	65 mA	Net weight (piece)	0.050 kg
Wattage equivalent	60 W		
Starting time (nom.)	0.5 s		
Power factor (nom.)	0.5		

## CorePro LEDlinear MV

### Dimensional drawing



Product	D	C
CorePro LED linear R7S 118mm 6.5-60W 830	22.5 mm	118 mm

LED 6.5-60W 830 R7S

