

Classic filament LED Lamps

CLA LEDBulb D 7.5-48W A60 B22 820 GOLD

Featuring a classic heritage design, Classic filament LED Lamps combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data


General Information		Power (Rated) (Nom)	
Cap base	B22 [B22]		7.5 W
Bulb shape	A60 [A 60mm]	Lamp current (nom.)	40 mA
Nominal lifetime (nom.)	15000 h	Wattage equivalent	48 W
Switching cycle	20000X	Starting time (nom.)	0.5 s
Technical type	7.5-48W	Warm-up time to 60% light (nom.)	0.5 s
		Power factor (nom.)	0.7
		Voltage (Nom)	220-240 V
Light Technical		Controls and Dimming	
Luminous flux (nom.)	600 lm	Dimmable	Yes
Luminous flux (rated) (nom.)	600 lm		
Colour designation	Flame	Approval and Application	
Correlated colour temperature (nom.)	2000 K	Energy-saving product	Yes
Luminous efficacy (rated) (nom.)	80 lm/W	Suitable for accent lighting	No
Colour consistency	<6	Energy efficiency label (EEL)	A+
Color rendering index (nom.)	80	Energy Consumption kWh/1000 h	8 kWh
LLMF at end of nominal lifetime (nom.)	70 %		
Operating and Electrical		Product Data	
Input frequency	50-60 Hz	Full product code	871869658741600

Classic filament LED Lamps

Order product name	CLA LEDBulb D 7.5-48W A60 B22 820 GOLD
EAN/UPC – product	8718696587416
Order code	58741600
Numerator – quantity per pack	1
Numerator – packs per outer box	10

Material no. (12NC)	929001257802
Net weight (piece)	0.030 kg

Dimensional drawing



filament A60 7W-48W 620lm 2000K B22 D

Product	D	C
CLA LEDBulb D 7.5-48W A60 B22 820 GOLD	60 mm	110.5 mm

Photometric data

General Uniform Lighting

