



MASTER LEDcandle

MASTER LEDcandle DT 6-40W B22 B38 CL

Delivering incandescent-like sparkling light effects, MASTER LEDcandle bulbs are ideal for general and decorative lighting in the hospitality industry, as well as in home environments. The dimmable MASTER LEDcandles drive further efficiencies, while helping to create the desired atmosphere. Mounted in full view in chandeliers, wall scones or modern luminaires, the clear or frosted glass bulbs fit all existing fixtures with an E14 and B15 socket. Drawing upon inputs from chandelier makers and designed to enhance the aesthetic appeal of the chandelier or luminaire, not only when lit but also when not, these lamps come in a classical slender shape with a unique, eye-catching lens design. They produce a beautiful sparkling warm light that delivers huge energy savings and minimizes maintenance cost. The flame-shaped candle lamps come in a classical slender shape with a unique, eye-catching lens design that perfectly complements modern LED candles.

Product data

• General Information

Cap-Base	B22 [B22]
Reddot Design Award Winner mark	Reddot Design Award Winner 2016
Bulb Shape	B38
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	6-40W

• Light Technical

Color Code	WW
Luminous Flux (Nom)	470 lm
Luminous Flux (Rated) (Nom)	470 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2200-2700 K
Luminous Efficacy (rated) (Nom)	75 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80

LLMF At End Of Nominal Lifetime (Nom)	70 %
---------------------------------------	------

• Operating and Electrical

Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	6.0 W
Lamp Current (Nom)	35 mA
Wattage Equivalent	40 W
Starting Time (Max)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	220-240 V

• Temperature

T-Case Maximum (Nom)	95 °C
----------------------	-------

• Controls and Dimming

Dimmable	Yes
----------	-----

• Mechanical and Housing

Bulb Finish	Clear
-------------	-------

PHILIPS

• **Approval and Application**


Suitable For Accent Lighting No
 Energy Efficiency Label (EEL) A+
 Energy Consumption kWh/1000 h 6 kWh

• **Product Data**

Full product code 871869645362900

Order product name MASTER LEDcandle DT 6-40W B22 B38 CL
 EAN/UPC - Product 8718696453629
 Order code 929001140802
 Numerator - Quantity Per Pack 1
 Numerator - Packs per outer box 10
 Material Nr. (12NC) 929001140802
 Net Weight (Piece) 0.063 kg


Dimensional drawing



B22 B38, B39

LED DT 6-40W B22 2200-2700K B38 CL

Product	D	C
MASTER LEDcandle DT 6-40W B22 B38 CL	38 mm	111 mm



© 2016 Philips Lighting Holding B.V.
 All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2016, October 10
 data subject to change