



CorePro LEDcandle

CorePro LEDcandle ND 5.5-40W E14 827 B35 CL

The frosted CorePro LEDcandle is designed for retrofit replacement of incandescent lamps. It is compatible with fixtures with an E14 holder and is an attractive product for chandeliers. LEDlamps deliver huge energy savings and minimize maintenance cost.

Product data


General Information		Warm-up time to 60% light (nom.)	
Cap base	E14 [E14]		instant full light
Bulb shape	B35 [B 35mm]	Power factor (nom.)	0.5
Nominal lifetime (nom.)	15000 h	Voltage (Nom)	220-240 V
Switching cycle	50000X	Temperature	
Technical type	5.5-40W	T-Case maximum (nom.)	95 °C
Light Technical		Controls and Dimming	
Luminous flux (nom.)	470 lm	Dimmable	no
Luminous flux (rated) (nom.)	470 lm	Mechanical and Housing	
Colour designation	Warm white (WW)	Bulb finish	Clear (CL)
Correlated colour temperature (nom.)	2700 K	Approval and Application	
Luminous efficacy (rated) (nom.)	85 lm/W	Suitable for accent lighting	No
Colour consistency	<6	Energy efficiency label (EEL)	A+
Color rendering index (nom.)	80	Energy Consumption kWh/1000 h	6 kWh
LLMF at end of nominal lifetime (nom.)	70 %	Product Data	
Operating and Electrical		Full product code	871869645479400
Input frequency	50-60 Hz	Order product name	CorePro LEDcandle ND 5.5-40W E14 827 B35 CL
Power (Rated) (Nom)	5.5 W	EAN/UPC – product	8718696454794
Lamp current (nom.)	50 mA	Order code	45479400
Wattage equivalent	40 W		
Starting time (nom.)	0.5 s		

CorePro LEDcandle

Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001142502

Net weight (piece)	0.040 kg
--------------------	----------

Dimensional drawing



Product	D	C
CorePro LEDcandle ND 5.5-40W E14 827 B35 CL	35 mm	106 mm

LED ND 5.5-40W E14 827 220-240V B35 CL

