



# MASTER LEDluster DiamondSpark

## MAS LEDlustre DT 6-40W E14 P48 CL

Delivering incandescent-like sparkling light effects, MASTER LEDluster bulbs are ideal for general and decorative lighting in the hospitality industry, as well as in home environments. The dimmable MASTER LEDlusters drive further efficiencies, while helping to create the desired atmosphere. Mounted in full view in chandeliers, wall scones or modern luminaires, the clear glass bulb fits all existing fixtures with an E14, E27 and B22 socket. Drawing upon inputs from chandelier makers and designed to enhance the aesthetic appeal of the chandelier or luminaire, not only when lit but also when not, these lamps come in a classical slender shape with a unique, eye-catching lens design. They produce a beautiful sparkling warm light that delivers huge energy savings and minimizes maintenance cost.

### Product data

General Information		Color rendering index (nom.)	
Cap base	E14 [ E14]		80
Bulb shape	P48	LLMF at end of nominal lifetime (nom.)	70 %
Nominal lifetime (nom.)	25000 h	Operating and Electrical	
Switching cycle	50000X	Input frequency	50-60 Hz
Technical type	6-40W	Power (Rated) (Nom)	6 W
Light Technical		Lamp current (nom.)	35 mA
Luminous flux (nom.)	470 lm	Wattage equivalent	40 W
Luminous flux (rated) (nom.)	470 lm	Starting time (nom.)	0.5 s
Colour designation	Warm white (WW)	Warm-up time to 60% light (nom.)	instant full light
Correlated colour temperature (nom.)	2200-2700 K	Power factor (nom.)	0.7
Luminous efficacy (rated) (nom.)	75 lm/W	Voltage (Nom)	220-240 V
Colour consistency	<6		

# MASTER LEDluster DiamondSpark

## Temperature

T-Case maximum (nom.)	95 °C
-----------------------	-------

## Controls and Dimming

Dimmable	yes
----------	-----

## Mechanical and Housing

Bulb finish	Clear (CL)
-------------	------------


## Approval and Application

Suitable for accent lighting	No
Energy efficiency label (EEL)	A+
Energy Consumption kWh/1000 h	6 kWh

## Product Data

Full product code	871869645358200
Order product name	MAS LEDlustre DT 6-40W E14 P48 CL
EAN/UPC – product	8718696453582
Order code	45358200
Local Code	MLED6WLUSDT14
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001140602
Net weight (piece)	0.072 kg

## Dimensional drawing



LED DT 6-40W E14 P48 CL

Product	D	C
MASTER LEDlustre DT 6-40W E14 P48 CL	48 mm	95 mm

