



# Classic filament LED Lamps

## CLA LEDLuster D 4.5-40W P45 E14 827 CL

Featuring a classic heritage design, Classic filament LED Lamps combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Product data

General Information	
Cap base	E14 [ E14]
Bulb shape	P45 [ P 45mm]
Nominal lifetime (nom.)	15000 h
Switching cycle	20000X
Technical type	4.5-40W
Light Technical	
Luminous flux (nom.)	470 lm
Luminous flux (rated) (nom.)	470 lm
Colour designation	Warm white (WW)
Correlated colour temperature (nom.)	2700 K
Luminous efficacy (rated) (nom.)	104.44 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50-60 Hz

Power (Rated) (Nom)	4.5 W
Lamp current (nom.)	29 mA
Wattage equivalent	40 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.7
Voltage (Nom)	220-240 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb finish	Clear (CL)


Approval and Application	
Energy-saving product	Yes
Suitable for accent lighting	No
Energy efficiency label (EEL)	A++

## Classic filament LED Lamps

Energy Consumption kWh/1000 h	5 kWh
<b>Product Data</b>	
Full product code	871869657559800
Order product name	CLA LEDLuster D 4.5-40W P45 E14 827 CL
EAN/UPC – product	8718696575598
Order code	57559800

Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001227402
Net weight (piece)	0.024 kg

### Dimensional drawing



filament 4.5W-40W 470lm NAD 2700K E14D

Product	D	C
CLA LEDLuster D 4.5-40W P45 E14 827 CL	45 mm	101.5 mm

Photometric data

General Uniform Lighting

