



280 G2 Microtower PC

Take on your work with the HP 280 MT desktop PC. Get the computing power you need for your business while minimizing the total cost of ownership—now that's a smart investment.

Dependable and ready for work

The HP 280 MT delivers reliable performance for your business with the tools you need for work. Enhance your meeting experience with the optional HP Conferencing Keyboard and HP Business Headset for collaboration.

Progressive style

Enjoy the full desktop experience on the scalable HP 280 MT with a functional design that compliments your workspace and is easy to set up and use.

Powered up processing

Cruise through tasks easily and efficiently with 6th Generation Intel® Core™ i3/i5 processors and up to 32 GB of powerful DDR4 memory for demanding applications.

Expansion options

PCIe x1 and PCIe x16 slots along with VGA and DVI-D ports, and an SSD drive option on the HP 280 Microtower help ensure broad compatibility with existing technology investments and future upgrades.

Manufacturer Part Number

V7Q84EA#ABU

Full Product Specifications

Note:

- *The full product specifications below are from the manufacturer and may contain information related to other package quantities that will not apply to the product that you are reviewing. Please confirm the actual content and/or package quantity from the main product specifications page.*
- *These specifications may represent the entire product series/model/line to which this product belongs with specific configuration differences between the individual products stated.*

- *These specifications may have been copied from the same product in other region/country in which case there might be minor differences in region-specific data such as Input Voltage, Terms of Warranty etc.*

Technical details

Operating system: Windows 10 Pro 64

Processor Chipset: Intel® H110

Processor speed: 3.2 GHz

Processor family: 6th Generation Intel® Core™ i5 processor

Processor: Intel® Core™ i5-6500 with Intel HD Graphics 530 (3.2 GHz, up to 3.6 GHz with Intel Turbo Boost, 6 MB cache, 4 cores)

Drives Hard drive description: 500 GB 7200 rpm SATA

Optical drive: Slim SATA SuperMulti DVD writer

External drive bays: One 13,3 cm (5.25") ODD

Internal drive bays: One 8,9 cm (3.5") HDD

One 8,9 cm (3.5") HDD (optional)

Storage type: HDD

Graphic Subsystem Graphics: Intel® HD Graphics 530

Graphics: Integrated

Multimedia Audio: Integrated Realtek ALC221VB with combo microphone/headphone jack, line-in and line-out rear ports (3.5 mm), internal speaker.

Input devices Pointing device: HP USB Mouse

Connectivity and Communications Network interface: Integrated 10/100/1000 GbE with Realtek RTL8111G-CG

Ports: 2 USB 2.0

1 microphone/headphone combo

Expansion slots: 1 PCIe x1

1 PCIe x16

1 PCI (optional)

1 SD media reader (optional)

Network interface type: LAN

I/O Port location: Front

Ports: 4 USB 2.0

2 USB 3.0

1 audio line in

1 audio line out

1 DVI-D

1 VGA

1 RJ-45

2 PS/2 (optional)

2 serial (optional)

1 parallel (optional)

I/O Port location: Back

Battery and Power Power: 180 W standard efficiency

180 W standard efficiency, active PFC

180 W, up to 85% efficient, active PFC

Weights Weight: 6.11 kg

System Components Form factor: Microtower

Security Management Security management: Trusted Platform Module (TPM) 1.2

Security cable slot

Software and Applications Software: HP business PCs are shipped with a variety of software titles including HP Recovery Manager, HP Support Assistant, CyberLink Power DVD BD, CyberLink Power2Go, and HP ePrint Driver. Please refer to this product's quick spec document for a full list of preinstalled

software.

Software footnote number: [11]

Dimensions Minimum dimensions (W x D x H): 17 x 35.5 x 35.88 cm

Memory Memory, standard: 4 GB DDR4-2133 SDRAM (1 x 4 GB)

Memory slots: 2 DIMM

Standard memory note: Transfer rates up to 2133 MT/s

Memory and storage: 4 GB memory

500 GB HDD storage

Warranty Warranty: 1-year (1-1-1) limited warranty and service offering includes 1 year of parts, labor and on-site repair. Terms and conditions vary by country. Certain restrictions and exclusions apply.

Published Date: September 23, 2016

V7Q84EA#ABU