

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0015979061](#)
Status: **Active**
Overview: Mini-Fit® TPA Plugs and Receptacles
Description: Mini-Fit® TPA Key for 6 Circuit

Documents:

[3D Model](#) [Packaging Specification PK-30072-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-5556-003 \(PDF\)](#)

General

Product Family Crimp Housings
Series [30072](#)
Application Power, Wire-to-Board, Wire-to-Wire
Overview [Mini-Fit® TPA Plugs and Receptacles](#)
Product Name Mini-Fit® TPA
UPC 800754203029

Physical

Circuits (maximum) 6
Color - Resin Natural
Gender Female
Glow-Wire Compliant No
Material - Resin Nylon
Net Weight 0.133/g
Number of Rows 2
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 4.20mm
Stackable No
Temperature Range - Operating -40°C to +105°C

Electrical


Current - Maximum per Contact 13.0A

Material Info

Engineering Number 30072-06NAT

Reference - Drawing Numbers

Packaging Specification [PK-30072-001-001](#)
Product Specification [PS-5556-003](#)
Sales Drawing [SD-30072-*](#)



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[30072](#) Series

Mates With

[30068](#) , [30069](#) , [30069](#) , [30070](#) , [30070](#) ,
[44473](#)

Use With

[30067](#) 4.20mm Pitch Mini-Fit® Crimp
Housing