


8903NWG



Aavid 8903 Screw Mounted Cover, pan head screws not provided - MS 51957-30 or equivalent recommended - secure the cover to the TO-3. At the typical mounting screw torque of .68 - .90 Nm (6-8 inch pounds), the TO-3 cover material cold-flows around the screw head to securely fasten the cover. Included are No.6 split washers as inserts to provide electrical connection of mounting screws to the TO-3 collector and an insulating snap-in cover for the screw heads. A test probe hole is provided in the top of the cover.

The 8903VB is made from thermoplastic polyester that meets the requirements of UL Bulletin 94 V-O. In addition to its excellent flammability rating, thermoplastic polyester offers resistance to most chemical environments, heat deflection temperature to 215.6°C (420°F) and UL continuous use temperature of 130 °C (266 °F).

Material: Nylon

Color: White

Flammability Standards: Self-extinguishing UL 94 V-2