

## Technical Information

Number of Screens

1

Screen Size

61 cm (24")

Screen Mode

Full HD

Response Time

1 ms

Aspect Ratio

16:9

Backlight Technology

LED

Panel Technology

Twisted Nematic Film (TN Film)

Tilt Angle

-5°to25°

Swivel Angle

No

Maximum Adjustable Height

No

## Video

Maximum Resolution

1920 x 1080

Standard Refresh Rate

60 Hz

Colour Support

16.7 Million Colours

Contrast Ratio

100,000,000:1

Brightness

250 cd/m<sup>2</sup>

## Interfaces/Ports

DVI

Yes

HDMI

Yes

VGA

Yes

## Power Description

Energy Efficiency Class

A

Energy Consumption per Year

34 kWh

Operating Power Consumption (EEL)

23 W

Operating Power Consumption (Energy Star)

20.09 W

Standby Power Consumption

450 mW

Off-Mode Power Consumption

350 mW

## Physical Characteristics

Colour

Black

Height

335.9 mm

Width

567 mm

Depth

52 mm

Height with Stand

421.20 mm

Width with Stand

567 mm

Depth with Stand

208 mm

Weight (Approximate)

3.25 kg

Weight with Stand (Approximate)

3.58 kg

## Miscellaneous

Package Contents

K242HL Widescreen LCD Monitor

Power Cord

1 x VGA Cable

Environmental Certification

MPR II

## Warranty

Warranty