

30V Hammer Drill

nutool



- Hammer action
- 2 Speed gearbox
- Keyless chuck
- Electronic speed control
- Electronic brake
- Forward and reverse action
- Multi-position side handle
- Additional battery
- Battery charge condition indicator
- Spirit level
- 1 Hr fast charge
- Soft grip & soft touch
- Supplied in a blow moulded case
- Supplied with 2 batteries

Technical Data

Voltage (V)	30
Battery Power Ni-d (Ah)	1.7
Speed/s (min-1)	0 - 330 / 0 - 1200
Drilling cap. wood (∅ mm)	30
Drilling cap. steel (∅ mm)	13
Drilling cap. concrete (∅ mm)	16
Chuck size (∅ mm)	2.0 - 13
Torque settings	8 + 1
Re-charge time (hr)	1
Weight (kg)	7.0

274103

Description	Order Code	price each
30V Cordless Hammer Drill	4745462	
30V Battery	5529955	