



HD 5/11 P 240V

Tough, highly portable professional cold-water pressure washer with upright or lie-flat operation.



1 First-class mobility

- The integrated carrying handle on the front of the machine enable easy loading and convenient transport.
- Compact design and low weight.

2 Flexibility

- Vertical and horizontal operation possible.
- Separate parking and transport position for the spray unit.

3 Quality

- The automatic pressure relief protects the components and extends the service life.
- High-quality brass cylinder head.

4 Practical accessory storage

- Screw connections (M 18 × 1.5) for storing surface cleaner directly on the machine.
- Practical nozzle compartments for triple nozzle and rotary nozzle.



HD 5/11 P 240V

- Save energy and time: EASY!Force high-pressure guns and EASY!Lock quick-release locks.

Technical data

Order Number	1.520-196.0	
EAN code	4054278053974	
Current type	Ph / V / Hz	1 / 240 / 50
Flow rate	l/h	490
Operating pressure	bar / MPa	110 / 11
Max. pressure	bar / MPa	160 / 16
Max. water feed temperature	°C	max. 60
Power rating	kW	2,2
Weight	kg	20,5
Dimensions (L x W x H)	mm	351 x 312 x 904

Equipment

Trigger gun	Easy-press trigger gun	
Trigger gun with soft grip	■	
High-pressure hose	m	10 / ID 6, 250 bar
Spray lance	mm	850
Anti-twist system (AVS)	■	
Pressure switch control	■	
Servo Control	-	

- Included in delivery.

ACCESSORIES FOR HD 5/11 P 240V

1.520-196.0

KÄRCHER



		Order Number	ID	Max. working pressure	Length	Price	Description	
Standard with unions on both sides								
High-pressure hose packaged	1	6.391-342.0	ID 8	315 bar	10 m			▲
High-pressure hose, 15 m DN 8, 315 bar, including rotary coupling	2	6.390-010.0	ID 8	315 bar	15 m		With rotary coupling, 2 x M 22 x 1.5	▲
High-pressure hose, 20 m DN 8, 315 bar, extension	3	6.390-031.0	ID 8	315 bar	20 m		With M 22x1.5 union at both ends and anti-kink protection ID 8/155°C/315 bar	▲
High-pressure hose, 30 m DN 8, including rotary coupling	4	6.390-293.0	ID 8	315 bar	30 m		With rotary coupling, 2 x M 22 x 1.5	▲
Longlife 400 with unions on both sides								
High-pressure hose Longlife 400, 10 m, DN 8, including rotary coupling	5	6.388-083.0	ID 8	400 bar	10 m		10 m high-pressure hose Longlife 400 (DN 8) with rotary coupling, two layer high-strength steel wire reinforced. Connectors at both ends. M 22 x 1.5, with kink protection.	▲
High-pressure hose packaged	6	6.391-354.0	ID 8	400 bar	10 m			▲
High-pressure hose Longlife 400, 15 m, DN 8, including rotary coupling	7	6.389-709.0	ID 8	400 bar	15 m		With rotary coupling, 2 x M 22 x 1.5	▲
High-pressure hose Longlife 400, 20 m, DN 8, extension	8	6.390-027.0	ID 8	400 bar	20 m		with rotary coupling, 2 x M 22 x 1.5	▲
High-pressure hose Longlife 400, 30 m DN 8, including rotary coupling	9	6.390-294.0	ID 8	400 bar	30 m		With rotary coupling, 2 x M 22 x 1.5	▲
Food industry version with unions on both sides								
High-pressure hose, 10 m ID 8, suitable for food industry, extension piece	10	6.389-479.0	ID 8	250 bar	10 m		10 m high-pressure hose (DN 8) with patented (rotating) AVS trigger gun connector. Non-discolouring outer layer for use in the food industry. M 22 x 1.5 with anti-kink sleeve.	▲
High-pressure hose, 20 m ID 8, suitable for food industry, extension piece	11	6.389-581.0	ID 8	250 bar	20 m		20 m high-pressure hose (DN 8) with swivel coupling. Non-discolouring outer layer for use in the food industry. Connectors at both ends, M 22 x 1.5, with kink protection. NW 8/155°C/250 bar.	▲
Longlife food industry version with unions on both sides								
High pressure hose food DN 8 / 10 m	12	6.391-864.0	ID 8	400 bar	10 m		Longlife HP hose for use in the food industry. Außendecke animal-grease-resistant, non-colour-bleeding material. With rotary coupling, 2 x M 22 x 1,5	▲
High-pressure hose food industry 400 bar, 20 m, DN 8, including rotary coupling	13	6.391-887.0	ID 8	400 bar	20 m			▲
Standard								
High-pressure hose, 10 m DN 6, AVS trigger gun connector	14	6.391-238.0	ID 6	250 bar	10 m		10 m high-pressure hose (M 22 x 1.5) with kink protection. With patented rotating AVS trigger gun connector and manual coupling. Further data: DN 6/155°C/250 bar.	■
HD-Schlauch DN 6, 15m	15	6.391-394.0	ID 6	250 bar	15 m			□
High-pressure hose, 10 m, DN 6, 300 bar, AVS trigger gun connection	16	6.391-875.0	ID 6	300 bar	10 m		With patented AVS connection in the trigger gun (pivot-mounted) and hand screw union. M 22 x 1.5 with anti-kink protection. NW 6/155°C/300 bar	□
High-pressure hose, 10 m DN 8, AVS trigger gun connector	17	6.390-025.0	ID 8	315 bar	10 m		10 m high-pressure hose (M 22 x 1.5) with kink protection. With patented rotating AVS trigger gun connector and manual coupling. Further data: DN 8/155°C/315 bar.	□
High-pressure hose, 15 m DN 8, AVS trigger gun connector	18	6.390-185.0	ID 8	315 bar	15 m		15 m high-pressure hose (M 22 x 1.5) with kink protection. With patented rotating AVS trigger gun connector and manual coupling. Further data: DN 8/155°C/315 bar.	□
High-pressure hose, 20 m DN 8, AVS trigger gun connector	19	6.390-171.0	ID 8	315 bar	20 m		20 m high-pressure hose (M 22 x 1.5) with kink protection. With patented rotating AVS trigger gun connector and manual coupling. Further data: DN 8/155°C/315 bar.	□

■ Included in delivery. □ Available accessories. ▲ Extension hose.

ACCESSORIES FOR HD 5/11 P 240V

1.520-196.0

KÄRCHER



		Order Number	ID	Max. working pressure	Length		Price	Description	
Longlife 400									
High pressure hose DN 6, 10 m, Longlife	20	6.391-882.0	ID 6	400 bar	10 m			With patented AVS connection in the trigger gun (pivot-mounted).	<input type="checkbox"/>
High-pressure hose packaged	21	6.391-351.0	ID 8	400 bar	10 m				<input type="checkbox"/>
High-pressure hose Longlife 400, 20 m DN 8, AVS trigger gun connector	22	6.390-208.0	ID 8	400 bar	20 m			20 m high-pressure hose Longlife 400 (DN 8) with patented (rotating) AVS trigger gun connector and manual coupling. Two layer high-strength steel wire reinforced.	<input type="checkbox"/>
Food industry version									
High-pressure hose 15 m ID 6, AVS trigger gun connector 11 mm, suitable for food industry, grey	23	6.391-654.0	ID 6	250 bar	15 m			15 m high-pressure hose (DN 6) with patented (rotating) AVS trigger gun connector. Non-discolouring outer layer for use in the food industry. DN 6/155°C/250 bar.	<input type="checkbox"/>
High-pressure hose, 10 m, DN 8, AVS trigger gun connection, food industry, grey	24	6.390-704.0	ID 8	250 bar	10 m			Food industry version, AVS connection in the trigger gun. grey NW 8/155 °C/250 bar	<input type="checkbox"/>
High-pressure hose, 20 m ID 8, AVS trigger gun connector, suitable for food industry, grey	25	6.390-705.0	ID 8	250 bar	20 m			20 m high-pressure hose (DN 8) with patented (rotating) AVS trigger gun connector. Non-discolouring outer layer for use in the food industry. NW 8/155°C/250 bar.	<input type="checkbox"/>
Longlife food industry version									
High-pressure hose Longlife 400, 15 m, ID 6, AVS trigger gun connection	26	6.391-888.0	ID 6	400 bar	15 m			Longlife HP hose for use in the food industry. Außendecke## animal-grease-resistant, non-colour-bleeding material. With patented AVS connection in the pistol (pivot mounted)	<input type="checkbox"/>
High-pressure hose Longlife 400, 10 m, ID 8, AVS trigger gun connection	27	6.391-885.0	ID 8	400 bar	10 m				<input type="checkbox"/>
High-pressure hose Longlife 400, 20 m, ID 8, AVS trigger gun connection	28	6.391-886.0	ID 8	400 bar	20 m				<input type="checkbox"/>

■ Included in delivery. □ Available accessories. ▲ Extension hose.

ACCESSORIES FOR HD 5/11 P 240V 1.520-196.0



		Order Number	Flow rate				Price	Description	
Easy Press high-pressure gun with holding power reduction (Kärcher patent)									
Easy press high-pressure trigger gun with softgrip	1	4.775-463.0						Easy press high-pressure trigger gun with softgrip. For high-pressure hoses DN 6 and DN 8 with 11 mm swivel diameter.	■

■ Included in delivery. □ Available accessories. ▲ Extension hose.

ACCESSORIES FOR HD 5/11 P 240V 1.520-196.0



1-2, 4



3

		Order Number	Nozzle size					Price	Description	
Power nozzle spray angle 15°										
Power nozzle 15036 - nur fuer Ersatz	1	2.885-225.0	36							■
HP nozzle spray angle 0°										
High-pressure nozzle spray angle 0°	2	2.884-533.0	40						High-pressure nozzle with powerful jet for extremely stubborn dirt.	□
Power nozzle spray angle 25°										
Power nozzle spray angle 25°	3	2.883-821.0	36						Fan jet nozzle with 25° spray angle, suitable for large areas and removing stubborn dirt and stains.	□
Power nozzle spray angle 40°										
Power nozzle spray angle 40°	4	2.884-522.0	40						Power nozzle with a 40° spray angle and fan jet, suitable for large areas and sensitive surfaces.	□

■ Included in delivery. □ Available accessories. ▲ Extension hose.

ACCESSORIES FOR HD 5/11 P 240V

1.520-196.0

KÄRCHER



		Order Number	Max. working pressure	Length		Price	Description	
Rotating spray lances								
Lance 850 mm, rotatable, ergonomic	1	4.760-663.0	300 bar	840 mm			850 mm stainless steel lance (manual coupling) with ergonomic handle for ease of use and protection. Rotatable 360° under pressure.	■
Rotatable lance, 600 mm, ergonomic	2	4.760-664.0	300 bar	600 mm			600 mm stainless steel lance (manual coupling) with ergonomic handle for ease of use and protection. Rotatable 360° under pressure.	□
1050 mm lance, rotatable, ergonomic	3	4.760-660.0	300 bar	1050 mm			1050 mm stainless steel lance (manual coupling) with ergonomic handle for ease of use and protection. Rotatable 360° under pressure.	□
Lance 1550 mm, rotatable, ergonomic	4	4.760-661.0	300 bar	1550 mm			1550 mm stainless steel lance (manual coupling) with ergonomic handle for ease of use and protection. Rotatable 360° under pressure.	□
Lance 2050 mm, rotatable, ergonomic	5	4.760-662.0	300 bar	2050 mm			2050 mm stainless steel lance (manual coupling) with ergonomic handle for ease of use and protection. Rotatable 360° under pressure.	□
Spray lances								
Anti-vibration lance	6	6.415-951.0	250 bar	950 mm			The spring-loaded 360° loop handle significantly reduces the vibrations on the spray lance, reducing the physical burden on the user, e.g. when working with the dirt blaster.	□
Double lance								
Double lance 960 mm	7	6.394-665.0	310 bar	960 mm			960 mm double lance for variable pressure adjustment on handle at full water flow rate. Suitable for agricultural use (e.g. stable cleaning).	□
Angular spray lance								
WC and gutter lance	8	4.760-073.0					Stainless steel lance WC and gutter with nozzle insert. Specially shaped for effective and hygienic cleaning of gutters and toilets.	□
Flexible spray lance								
Flexible lance 1050 mm	9	6.394-654.0	210 bar	1050 mm			1050 mm flexible lance with variable bend from 20° to 140°, ideal for cleaning difficult to reach areas, e.g. gutters.	□
Telescopic spray lance								
Telescopic jet pipe	10	6.394-690.0	225 bar					□
Restraint belt for telescopic jet pipe	11	6.373-987.0					Convenient strap for relief when working with the telescopic spray lance (6.394-690). The burden is optimally distributed on the body and longer periods of use are possible.	□
Gutter cleaner								
Gutter cleaning lance	12	2.642-305.0					The lance is suited for cleaning of gutter systems. Because of the shape of the lance and the special nozzle the gutter can be cleaned without removing the cover plates.	□
Undercarriage spray lance								
Underbody lance	13	4.760-245.0		700 mm			Stainless steel lance for effective and easy underbody and wheel arch cleaning. Without high-pressure nozzle.	□

■ Included in delivery. □ Available accessories. ▲ Extension hose.

ACCESSORIES FOR HD 5/11 P 240V 1.520-196.0

KÄRCHER



		Order Number	Flow rate	Nozzle size	Diame- ter	Price	Description	
Hard surface cleaner FR Classic								
	1	2.643-476.0						<input type="checkbox"/>
Hard surface cleaner FR Basic								
FR Xpert	2	2.642-998.0			300 mm			<input type="checkbox"/>
Hard surface cleaner FR 30								
FR 30	3	2.642-997.0			300 mm			<input type="checkbox"/>
Hard surface cleaner FR 30 ME								
FR 30 ME surface cleaner	4	2.640-355.0			300 mm		Hot water resistant stainless steel surface cleaner with double ceramic bearings, non-marking swivel castors and suction hose connection. Ideal for indoor cleaning, e.g. food industry.	<input type="checkbox"/>
Machine-specific nozzle kit for FR								
Nozzle kit for surface cleaners (type-specific) 450 - 500 l/h	5	2.640-482.0	450-500 l/h				Nozzle kit includes power nozzles and unions. For Kärcher surface cleaners (450 to 500 l/h).	<input type="checkbox"/>
Machine-specific nozzle kits for FR Classic								
	6	2.885-312.0		40				<input type="checkbox"/>
Adapter for home & garden pressure washers								
Adapter FR mit Consumer-Geräte	7	4.762-402.0						<input type="checkbox"/>

■ Included in delivery. □ Available accessories. ▲ Extension hose.

ACCESSORIES FOR HD 5/11 P 240V 1.520-196.0



		Order Number	Max. working pressure	Nozzle size			Price	Description
Triple nozzles								
Triple nozzle 036	1	4.767-148.0	300 bar	36				Triple nozzle with manual nozzle changeover. Convenient spray adjustment. For high-pressure cleaners with injector; low-pressure fan jet for detergent removal and application. Connector M 18x1.5. <input type="checkbox"/>
Dirt Blaster, small								
Dirt blaster	2	4.767-023.0	180 bar	40				The dirt blaster with rotating pencil jet offers 10 times better cleaning performance. Ceramic nozzle and bearing ring for a long service life. Further data: Max. 180 bar, 18 MPa, 60°C. <input type="checkbox"/>
	3	4.767-231.0	180 bar	40				<input type="checkbox"/>

■ Included in delivery. □ Available accessories. ▲ Extension hose.

ACCESSORIES FOR HD 5/11 P 240V 1.520-196.0




		Order Number	Nozzle size					Price	Description	
Wet blasting attachment (without nozzle)										
Wet blasting attachment with flow control (without nozzles)	1	4.762-010.0							Paint, rust and scale removal made easy: Kärcher wet blasting attachment with flow control for adding blasting abrasive to the high-pressure jet.	<input type="checkbox"/>
Wet blasting attachment without flow control (nozzles not included)	2	4.762-022.0							Paint, rust and scale removal made easy: Kärcher wet blasting attachment with flow control for adding blasting abrasive to the high-pressure jet. Without flow control.	<input type="checkbox"/>
Nozzle pack for wet blasting attachment										
Nozzle kit for wet blasting attachment 035	3	2.638-526.0	35						Nozzle kit with wet blasting nozzle and nozzle insert (type specific). For optimal Kärcher wet blasting attachment performance. Only in combination with wet blasting attachment 4.762-010/-022.	<input type="checkbox"/>
Boron carbide nozzle										
Boron carbide nozzle, for machines as of 1000 l/h	4	6.415-084.0	6 mm						In addition to nozzle packs. Very wear-resistant nozzle with boron carbide chuck for continuous-duty operation.	<input type="checkbox"/>

■ Included in delivery. □ Available accessories. ▲ Extension hose.

ACCESSORIES FOR HD 5/11 P 240V 1.520-196.0

KÄRCHER



		Order Number	Max. working pressure	Nozzle size	Diame-ter		Price	Description
Pipe cleaning hose, ID 6								
Pipe cleaning hose	1	6.390-028.0	120 bar					20 m flexible high-pressure hose (DN 6) for cleaning pipes (threaded connection for R 1/8 nozzle). <input type="checkbox"/>
Pipe cleaning hose, DN 6, 30 m	2	6.390-029.0	120 bar					30 m flexible high-pressure hose (DN 6) for cleaning pipes (threaded connection for R 1/8 nozzle). <input type="checkbox"/>
Pipe cleaning hose, DN 6, 20 m, 220 bar	3	6.390-030.0	250 bar					20 m flexible high-pressure hose (DN 6) for cleaning pipes up to 220 bar (threaded connection for R 1/8 nozzle). <input type="checkbox"/>
Pipe cleaning nozzle								
Drain cleaning dirt blaster D 25/040	4	6.415-944.0		40	25 mm			The forward-tilted rotating pencil jet removes the most stubborn dirt. The three backwards-tilted jets ensure the necessary forward movement, as well as convenient handling. <input type="checkbox"/>
Drain cleaning dirt blaster D 30/040	5	6.415-946.0		40	30 mm			
Drain cleaning dirt blaster D 35/040	6	6.415-948.0		40	35 mm			
Pipe cleaning nozzle	7	5.763-015.0		55	16 mm			16 mm pipe cleaning nozzle with internal thread. Various jet directions for environmentally-friendly cleaning of blocked drains and pipes. <input type="checkbox"/>
	8	5.763-017.0		50	30 mm			30 mm pipe cleaning nozzle with internal thread. Various jet directions for environmentally-friendly cleaning of blocked drains and pipes. <input type="checkbox"/>
Rotating pipe cleaning nozzle	9	6.415-428.0		50	16 mm			Rotating pipe cleaning nozzle with internal thread and four rotating jets for environmentally-friendly cleaning of blocked drains and pipes. <input type="checkbox"/>

■ Included in delivery. □ Available accessories. ▲ Extension hose.

ACCESSORIES FOR HD 5/11 P 240V 1.520-196.0



1



2

		Order Number	Flow rate				Price	Description	
Cup foam lance									
Foam lance nozzle Ø1,5	1	6.394-969.0							<input type="checkbox"/>
Foam nozzle mounting kit									
Foam nozzle kit	2	2.637-926.0						Foaming agent kit. The foam nozzle is ideal for use in sanitary areas and the food industry and wherever long application times are necessary.	<input type="checkbox"/>

■ Included in delivery. □ Available accessories. ▲ Extension hose.

ACCESSORIES FOR HD 5/11 P 240V 1.520-196.0



		Order Number	Length				Price	Description	
Automatic, self-winding hose reels									
Swivel holder	1	2.639-931.0						Swivel holder for automatic hose reel wall mounting. For maximum action radius and flexibility of high-pressure hose. Rotatable 120°. Galvanised steel.	<input type="checkbox"/>
ABS wall fastening stainless steel	2	2.641-867.0						Swivelling wall bracket made of high-grade steel (for 2.641-866). This makes maximum flexibility and convenience possible when working with the HP hose.	<input type="checkbox"/>
Add-on kit hose reel plastics	3	6.392-975.0	20 m					Automatic hose reel for 20 m high-pressure hose. The console is made from powder-coated steel, the drum is made from plastic.	<input type="checkbox"/>
Add-on kit hose reel	4	6.392-965.0	20 m					Automatic hose reel for 20 m high-pressure hose. The console consists of stainless steel, the drum is made from plastic.	<input type="checkbox"/>
Hose reel, automatic, 20 m, painted	5	2.639-919.0	20 m					Automatic hose reel of durable plastic. Painted steel bracket. Suitable for 20 m high-pressure hose.	<input type="checkbox"/>
Hose reel, automatic, 20 m, stainless steel	6	6.391-421.0	20 m					Automatic stainless steel hose reel. With swivel holder. Suitable for 20 m high-pressure hose.	<input type="checkbox"/>
ABS hose reel stainless steel	7	2.641-866.0	20 m					High-grade, automatic steel hose reel. Especially suitable for use in the food industry. The material and finish provide for a corrosion-resistant, watertight capsuled sprong drive. Connection for HP hoses with nipple.	<input type="checkbox"/>

■ Included in delivery. □ Available accessories. ▲ Extension hose.

ACCESSORIES FOR HD 5/11 P 240V

1.520-196.0

KÄRCHER



		Order Number	Length	Diameter	Price	Description	
Starting current limiter							
Starting current limiter	1	2.637-495.0				Reduces starting current in single-phase supply and protects line fuse.	<input type="checkbox"/>
Geka coupling							
With hose nozzle, R 1/2"	2	6.388-461.0				with hose liner	<input type="checkbox"/>
With hose nozzle, R 3/4"	3	6.388-455.0					<input type="checkbox"/>
With female thread, R 3/4"	4	6.388-473.0				with female thread	<input type="checkbox"/>
Suction filter							
Water filter	5	6.414-956.0					<input type="checkbox"/>
Suction filter with check valve	6	4.730-012.0				Brass suction filter suitable for ponds, storage tanks, etc. With check valve.	<input type="checkbox"/>
Fine-mesh water filter							
Fine-mesh water filter with adapter	7	4.730-102.0				Fine-mesh water filter, 125 µm, max. temperature 50°C. Protects the high-pressure cleaner from dirt particles contained in the water. Water flow rate up to 1200 l/h. Connection 3/4", with adapter, 1".	<input type="checkbox"/>
Water supply hose							
Water supply hose	8	4.440-038.0	7,5 m			NW 13 R1" / R 3/4", up to 30 °C	<input type="checkbox"/>
	9	4.440-207.0	7,5 m			NW 19 R1" / R 3/4", up to 85 °C, for pick-up	<input type="checkbox"/>
Backflow check valve							
Backflow preventer	10	2.641-374.0				To prevent detergent getting into the drinking water cycle in case of inlet at low-pressure. - hot water resistant up to 80 °C - tested according to IEC 60335-2-79 - integrated leakage protection	<input type="checkbox"/>

■ Included in delivery. □ Available accessories. ▲ Extension hose.

ACCESSORIES FOR HD 5/11 P 240V 1.520-196.0



1



2

		Order Number	Flow rate				Price	Description	
Rotating washing brush									
	1	4.762-561.0	500-800 l/h						<input type="checkbox"/>
	2	4.762-560.0	500-800 l/h						<input type="checkbox"/>

■ Included in delivery. □ Available accessories. ▲ Extension hose.