

## Basic

Brand Name:	Lenovo
Colour:	Black
DisplayPort:	Yes
Energy Star:	Yes
Environmentally Friendly:	Yes
Form Factor:	Small Form Factor
Graphics Controller	Intel
Manufacturer:	
Graphics Controller Model:	HD Graphics 530
Graphics Memory Accessibility:	Shared
Graphics Memory Technology:	DDR4 SDRAM
Monitor Included:	No
Number of USB 2.0 Ports:	2
Number of USB 3.0 Ports:	4
Operating System Architecture:	64-bit
Operating System Platform:	Windows
Operating System:	Windows 10 Pro
Optical Drive Type:	DVD-Writer
Processor Manufacturer:	Intel
Processor Model:	i5-6400
Processor Speed:	2.70 GHz
Processor Type:	Core i5
Product Family:	S510
Product Type:	Desktop Computer
Screen Size:	No
Standard Memory:	4 GB
Total Number of USB Ports:	6
Total Solid State Drive Capacity:	128 GB
VGA:	Yes
Wireless LAN:	No

## Display & Graphics

Graphics Controller	Intel
Manufacturer:	
Graphics Controller Model:	HD Graphics 530
Graphics Memory Accessibility:	Shared
Graphics Memory Technology:	DDR4 SDRAM
Monitor Included:	No
Screen Size:	No

## General Information

Brand Name:	Lenovo
Manufacturer Part Number:	10KY003NUK
Manufacturer Website Address:	<a href="http://www.lenovo.com/uk/en/">http://www.lenovo.com/uk/en/</a>
Manufacturer:	Lenovo Group Limited
Product Model:	10KY003NUK
Product Name:	S510 10KY003NUK Desktop Computer
Product Series:	S510
Product Type:	Desktop Computer

## Interfaces/Ports

DisplayPort:	Yes
Number of USB 2.0 Ports:	2
Number of USB 3.0 Ports:	4
Total Number of USB Ports:	6
VGA:	Yes

## Memory

Memory Technology:	DDR4 SDRAM
Standard Memory:	4 GB

## Miscellaneous

Energy Star:	Yes
Environmental Certification:	ENERGY STAR 6.1
Environmentally Friendly:	Yes
Features:	Security Slot
Package Contents:	

- S510 10KY003NUK Desktop Computer
- Keyboard
- Mouse

## Network & Communication

Wireless LAN: No

### **Physical Characteristics**

Colour: Black  
Depth: 320 mm  
Form Factor: Small Form Factor  
Height: 88.9 mm  
Weight (Approximate): 4.13 kg  
Width: 294.6 mm

### **Processor & Chipset**

Processor Generation: 6th Gen  
Processor Manufacturer: Intel  
Processor Model: i5-6400  
Processor Speed: 2.70 GHz  
Processor Type: Core i5

### **Software**

Operating System Architecture: 64-bit  
Operating System Platform: Windows  
Operating System: Windows 10 Pro

### **Storage**

Optical Drive Type: DVD-Writer  
Optical Media Supported: DVD-RAM/±R/±RW  
Total Solid State Drive Capacity: 128 GB

### **Warranty**

Limited Warranty: 1 Year