



Point Caliper Series 573,536-ABSOLUTE Digimatic and Vernier Type



Series 573

FEATURES

- Narrow tip jaws fit into very small grooves and tracks, making many previously difficult outside measurements far easier to obtain. With depth bar.
- With SPC data output. (Series 573)
- Supplied in fitted plastic case

Technical Data

Accuracy: Refer to the list of specifications. (excluding quantizing error for digital models)

Resolution*: 0.01mm or .0005"/0.01mm

Graduation**: 0.05mm

Display*: LCD

Length standard*: ABSOLUTE electrostatic capacitance type linear encoder

Max. response speed*: Unlimited

Battery*: SR44 (1 pc.), **938882**




Battery life*: Approx. 3.5 years under normal use

*Digital models **Analog models

Function of Digital Model

Origin-set, Zero-setting, Power On/Off, Data output, inch/mm conversion (inch/mm models)

Alarm: Low voltage, Counting value composition error

Order Number	573-721	573-725
Image		-
Parts	 Parts Break Down	 Parts Break Down
Range	0-6in 0-150mm	0-6in 0-150mm
Accuracy	.001in	.001in
LCD Resolution	.0005in 0.01mm	.0005in 0.01mm
Mass	163g	163g