



INSTALITE ZH-150 Raychem Sleeving

Lightweight High-Temperature, Zerohal Heat-Shrinkable Tubing

ADVANCED PERFORMANCE

- Unique, lightweight crosslinked material
- Halogen free, flame retarded, fluid resistant
- Ruggedized, abrasion resistant
- Operating temperature range: -75°C to 150°C

APPLICATION VERSATILITY

- 2 to 1 shrink ratio, in eight sizes
- Limited fire hazard
- Metric sizing

FAST, EASY INSTALLATION

- Lightweight material
- Highly flexible for easy handling
- Single system for multiple application environments

APPLICATIONS

- Military
- Marine
- Rail and Mass Transit

INSTALITE ZH-150 tubing from TE Connectivity (TE) is the first heat-shrinkable tubing to combine high-temperature and zero halogen properties in a lightweight material.

Unique Material, Exceptional Properties

TE's groundbreaking INSTALITE ZH-150 heat-shrink tubing helps you meet existing and future requirements for zero halogen, limited fire hazard tubing with high-temperature properties. The tubing helps provide excellent mechanical and electrical protection for wire and cable harnesses across multiple environments.

This new breakthrough in material science provides a heat-shrink product that can deliver protection for people and equipment in a high-temperature, lightweight product.

TE Components . . . TE Technology . . . TE Know-how . . .

AMP | AGASTAT | CII | HARTMAN | KILOVAC | MICRODOT | NANONICS | POLAMCO | Raychem | Rochester | DEUTSCH
SEACON Phoenix | LL Rowe | Phoenix Optix | AFP | SEACON

Get your product to market faster with a smarter, better solution.

INSTALITE ZH-150 Sleeving

Lightweight High-Temperature, Zerohal Heat-Shrinkable Tubing



Specifications

MATERIALS

- **Lightweight, crosslinked material:** Zerohal material, flame retarded

HEAT-SHRINK CHARACTERISTICS

- **Shrink Ratio:** 2 to 1
- **Minimum Shrink Temperature:** 150°C
- **Minimum Full Recovery Temperature:** 175°C

ENVIRONMENTAL

- **Operating Temperature Range:** -75°C to 150°C
- **Flammability:** Limited fire hazard
- **Fluid Resistance:** Resists common aerospace and military fluids
- **Flexibility:** Very flexible tubing
- **Mechanical:** Ruggedized, abrasion resistant

STANDARDS/SPECIFICATIONS

- **Application Specification:** ELE-3COP-551
- **Product Specification:** RW-3044

Size	Inside Diameter		Wall Thickness After Recovery (nom.)	Mass Grams/m (±10%)	Part Description	Part No.
	As Supplied (min.)	After Recovery (max.)				
3.0/1.5	3.0 (0.118)	1.5 (0.059)	0.70 (0.028)	4.2	ZH150-3/1.5-0-SP	EH3261-000
5.0/2.5	5.0 (0.197)	2.5 (0.098)	0.75 (0.030)	8.92	ZH150-5/2.5-0-SP	EH3263-000
8.0/4.0	8.0 (0.315)	4.0 (0.157)	0.80 (0.031)	13.00	ZH150-8/4-0-SP	EH3264-000
12.0/6.0	12.0 (0.472)	6.0 (0.236)	0.90 (0.035)	20.94	ZH150-12/6-0-SP	EH3265-000
18.0/9.0	18.0 (0.709)	9.0 (0.354)	1.00 (0.039)	31.96	ZH150-18/9-0-SP	EH3267-000
24.0/12.0	24.0 (0.945)	12.0 (0.472)	1.10 (0.043)	50.69	ZH150-24/12-0-SP	EH3268-000
40.0/20.0	40.0 (1.575)	20.0 (0.789)	1.30 (0.051)	94.1	ZH150-40/20-0-SP	EH3269-000
50.0/30.0	50.0 (1.969)	30.0 (1.181)	1.50 (0.059)	160	ZH150-50/30-0-SP	EH3270-000

Dimensions: mm (inch)

INSTALITE ZH-150 Comparison

	Temperature Range	Low Smoke	Flexibility	Low Toxicity	Light Weight	Fluid Resistance
ZH-150	Excellent	Very Good	Excellent	Very Good	Excellent	Excellent
ZHTM	Good	Excellent	Good	Excellent	Good	Good
DR25	Excellent	—	Excellent	—	Very Good	Excellent

te.com/zh150

© 2016 TE Connectivity Ltd. family of companies. All Rights Reserved.

1-1773896-9 11/16

AMP, AGASTAT, CII, DEUTSCH, HARTMAN, INSTALITE, KILOVAC, LL Rowe, MICRODOT, NANONICS, POLAMCO, Raychem, SEACON, Zerohal, TE, TE Connectivity and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies.

Other products, logos, and company names mentioned herein may be trademarks of their respective owners.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information herein, nothing herein constitutes any guarantee that such information is error-free, or any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. The TE entity issuing this publication reserves the right to make any adjustments to the information contained herein at any time without notice. All implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose are expressly disclaimed. The dimensions herein are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice.

Consult TE for the latest dimensions and design specifications.

North America +1 800 522 6752 • Asia Pacific +86 0 400 820 6015 • France +33 1 34 20 86 86 • Germany +49 6251 133 1999 • United Kingdom +44 800 267 666
Visit te.com for additional country contacts.