

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1600140003](#)
Status: **Active**
Overview: [stAK50h™ Infotainment Connector System](#)
Description: [stAK50h™ Hybrid Receptacle, 28 Circuits, Key 3, Light Gray, Bag](#)

Documents:

Drawing (PDF)	Packaging Specification PK-31302-266 (PDF)
Product Specification PS-160014-9001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-160014-001-001 (PDF)	Product Literature (PDF)

General

Product Family	Crimp Housings
Series	160014
Application	Power, Signal, Wire-to-Board
Overview	stAK50h™ Infotainment Connector System
Product Literature Order No	987651-5191
Product Name	stAK50h™
UPC	887191923239

Physical

Circuits (maximum)	28
Color - Resin	Gray (Light)
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS
Net Weight	4.846/g
Number of Rows	5
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm, 4.00mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40°C to +85°C

Electrical

Current - Maximum per Contact	Contact Molex
-------------------------------	---------------

Material Info

Reference - Drawing Numbers

Application Specification	AS-160014-001-001
Packaging Specification	PK-31302-266
Product Specification	PS-160014-9001
Sales Drawing	SD-160014-0001, SD-160014-002



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Contained Per -
ED/21/2016 (20 June
2016)

N,N-
dimethylacetamide

Halogen-Free

Status

Not Relevant

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[160014 Series](#)

Mates With

[stAK50h Header Assemblies 160013](#)

Use With

TE Connectivity NanoMQS 0.50mm
Terminal|Delphi OCS / JST MSA 1.20mm
Terminal