

Alnico Button Magnet datasheet

- Alnico 5 magnet material
- Magnetically stable at high temperatures
- Max. operating temperature 220°C
- Mild steel pot, aluminium spacer.
- Zinc plated body
- Diameter ground to H6 tolerance
- Custom designs available



Product Information

Product No.	Eclipse Magnetics Product No.	Diameter	Height	Slot Size (Min–Max) <i>mm</i>	Hole size	Weight <i>kg</i>	Pull force
TL16101	E821	12.7	9.5	4.0–7.2	4.4	0.006	0.7
TL16102	E822	19.1	12.7	5.6–8.7	4.8	0.020	1.9
TL16103	E823	25.4	15.9	5.6–8.7	4.8	0.050	3.4