

Alnico power magnets datasheet

- 550° maximum operating temperature
- Alnico 5 magnet material
- Good corrosion resistance



Product Information

Product No.	Eclipse Magnetics Product No.	Length (mm)	Width (mm)	Height (mm)	Width of Gap (mm)	Hole Size	Hole Centres	Weight (kg)	Weight per Pair (kg)	Pull Force (kg)
TL16110	811	30	20	20	15	5	N/A	0.06	0.06	4.5
TL16111	812	40	25	25	20	5	N/A	0.12	0.12	9
TL16112	813	45	30	30	23	5	N/A	0.18	0.18	11.8
TL16113	814	57	44.5	35	27.8	2 X 7.9	31.75	0.37	0.37	23.5