

Alnico pocket magnets datasheet

- 550° maximum operating temperature
- Alnico 5 magnet material
- Good corrosion resistance



Product Information

Product No.	Eclipse Magnetics Product No.	Length (mm)	Width (mm)	Height (mm)	Width of Gap (mm)	Weight per Pair (kg)	Pull Force (kg)
TL16114	E802	28.5	7.6	25.4	6.3	0.03	2.4
TL16115	E803	33.3	15.9	35	7.9	0.09	4