

# NITRO 4x5

8 CHN 1080P HI-DEF TVI, AHD, 960H, IP, CVI - NVR

HDMI

Full HD  
1080P

WD Purple

5 IN 1  
NVR



5x

## 5 In 1 Formats

This NVR supports High-Definition Transport Video (HD-TVI), Analogue High Definition (AHD), 960H, Internet Protocol (IP) and High Definition Composite Video Interface (CVI) recording formats.

# NITRO 4x5

## NITRO 4X5 NVR KEY FEATURES

- P2P No Port Forwarding
- Real Time 1080P Recordings
- HDMI/VGA Monitor Outputs
- PTZ Control
- USB Backup
- Motion Detection
- 4 Channel Playback
- 4 Alarm Inputs
- Arc Compatible
- 5-in-1 NVR



## Widescreen Footage

1080P formatting also means that images are recorded in a widescreen format which suits modern TV's and monitors, meaning images do not get stretched or squeezed to fit on screen.



## Scheduled Recording

Set the NVR to record at specific times of the day or for set periods when you are at work, away for weekends or on holiday.

NEW QV PRO

DEDICATED APPS  
FOR SMART PHONE  
& TABLET



1080P  
1920 X 1080



960H  
960 X 576

720P  
1280 X 720

# NITRO 4x5

8 CHN 1080P HI-DEF TVI, AHD, 960H, IP, CVI - NVR



<b>Model</b>	<b>4x5-8 Channel</b>
<b>VIDEO</b>	
Video Codec	H.264
Encode	8*4M@6fps(AHD); 8*3M@8fps(AHD); 8*1080P@12fps(5-in-1)
Decode	4*4M@6fps(AHD); 4*3M@8fps(AHD); 4*1080P@12fps(5-in-1)
Multi-mode Input	Pure Analog: 8*1080P Pure Network: 8*1080P; 16*960P; 4*3M; 4*5M
Onvif	Support
<b>AUDIO</b>	
Audio Compression	G.711A
Intercom	Support
<b>RECORDING AND PLAYBACK</b>	
Record Mode	Manual>alarm>motion detection>timing
Playback Channels	4 (pure local input mode)
<b>STORAGE</b>	
Backup Mode	Network backup, USB HDD, USB writer, SATA writer
<b>INTERFACE</b>	
Video Input	8 BNC
Video Output	1ch VGA, 1ch HDMI
Audio Input	8ch RCA
Audio Output	1ch RCA
Alarm Input	4
Alarm Output	1
Network Interface	RJ45 10M/100M Adaptive Ethernet port
PTZ Control	RS485; Support multiple PTZ protocols
USB	2 USB ports
Hard Disk	1 SATA (Each maximum support 6T)
Power	12V/2A
Dimension	310mm (Length) x 230mm (Width) x 44mm (Height)

HDMI

Full HD  
1080P



# NITRO 4x5

