



LCD SDI COLOUR MONITOR

Model No. L320SDI

31.5" TFT LCD SDI Full HD Colour Monitor, LED Back Light, 1920 x 1080P, Inputs SDI In/Out, HDMI, DVI, VGA, 2 x Composite Video In/Out BNC. Y/C (S-Video) In/Out, 2 x Audio In/Out and via Speakers, I/R Remote Control. **Options:** Glass Front. Other sizes available.



Main Features:

- Resolution: 1920 x 1080P – Full HD
- Picture Ratio: 16:9
- Brightness: 350 cd/m2 - LED Back light.
- Contrast Ratio: 3000:1
- Inputs: SDI, HDMI, DVI, VGA, S-Video
2 x Composite Video BNC, Audio.
- Outputs: SDI, 2 x Comp Video, S-Video, Audio
- PIP/POP Function VGA/Video.
- Mounting: VESA 100 or 200, Key Hole, Stand.
- 3D De-Interlaced Technology.
- Anti-blur/image auto. • Fast Response Time.
- Slim Aluminium cabinet in Black.
- Speaker 2 x 2 Watts max.

The L320SDI with Full HD TFT technology offers Professional sharp images coupled with a high contrast ratio gives superb pictures. SDI In/Out, Composite video In/Out both with BNC Connectors makes this is a truly versatile Monitor. Also boasting various mounting options and finished in a Smart tough Aluminium Metal housing. This compact unit is ideal for Multimedia Video and Surveillance system applications.

SPECIFICATIONS:

- Active area: 698.4 x 392.8 (WxH)mm. • 16.7M Colours. • PAL and NTSC Auto.
- Response Time: 6.5 ms (G to G). • Viewing angle: Left/Right: 89°, Up/ Down 89°.
- SDI Standard: 3G-SDI (SMPTE 424M), HD-SDI (SMPTE 292M) SD-SDI (SMPTE 259M).
- SDI Video: 3G-1080P50/60 (4:2:2), HD-720P50/60 & 1080i50/60, 1080P25/30Hz, SD-NTSC/60Hz, PAL/50Hz.
- SDI Bandwidth: 2.97 Gbps, 2.975 / 1.001 Gbps.
- Controls/Indicators: Front: On LED, I/R sensor. Rear: Source, Menu, Item, Up, Down, Power.
- Power Source: 100-240 Vac 50/60Hz 57 Watts.
- Dimensions: 761 x 454.6 x 78.7 (93.2 with stand). Carton: 895 x 670 x 44 (WxHxD)mm.
- Weight: Unit: 13.2 Kgms, Carton: 14.98 Kgms. • Temp: Operation: 0°C~40°C, Storage: -20~ 60°.

Connections: SDI In/Out: BNC, sockets. Full HD: HDMI socket. DVI: DVI-D socket. Composite Video 1 & 2 In/Out: BNC sockets. VGA: 15 pin Sub-D. S-Video (Y/C): In/Out 4 pin mini din socket. Audio 1 & 2 In/Out Right and Left: Phono sockets. PC Audio In: 3.5mm jack socket. AC input: IEC socket. USB for Media and Service use only.

Standard accessories: AC Mains Lead, I/R Remote Control.

- All information correct at time of going to press. Design and specification are subject to change without prior notice. E&EO

Product Shop International Ltd

Unit 2 Whitway Farm, Winchester Road, Burghclere, RG20 9LE. UK

e-mail: sales@productshop.co.uk Website www.productshop.co.uk

Tel: +44 (0) 844 800 4433

Registered office: As above. Registered No. 3852764 VAT No. GB 727 0478 29