


Tantalum, MnO2 Tantalum, Commercial Grade, T110, 2.2 uF, 10%, 35 V, 5 Ohms



Dimensions	
<b>D</b>	4.7mm +/-0.25mm
<b>L</b>	12.04mm +/-0.79mm
<b>L2</b>	15.49mm
<b>LL</b>	38.1mm +/-6.35mm
<b>F</b>	0.51mm +/-0.05mm

Packaging Specifications	
<b>Packaging:</b>	Bulk, Box
<b>Packaging Quantity:</b>	75

General Information	
<b>Dielectric:</b>	MnO2 Tantalum
<b>Style:</b>	Axial Hermetic
<b>Series:</b>	T110
<b>Description:</b>	Axial, Solid Tantalum, Hermetically Sealed, Military (Non-ER), Polar
<b>Features:</b>	Polar
<b>RoHS:</b>	Yes
<b>Termination:</b>	Tin
<b>Lead:</b>	Wire Leads, Uninsulated
<b>Construction:</b>	Hermetic
<b>Notes:</b>	When Supplied On T&R Or Ammo, Lead Length Is Determined By Taping Specification

Specifications	
<b>Capacitance:</b>	2.2 uF
<b>Capacitance Tolerance:</b>	10%
<b>Voltage DC:</b>	35 VDC (85C), 28 VDC (125C Surge), 0.35 V (125C Reverse)
<b>Temperature Range:</b>	-55/+125C
<b>Rated Temperature:</b>	85C
<b>Resistance:</b>	5 Ohms (100kHz)
<b>Leakage:</b>	1 uAmps (25C)