


Ceramic, Commercial Grade, CA064, 2200 pF, 10%, 200 V, 0612, X7R, SMD, MLCC, Array, Flex Termination, Auto Grade



#### Dimensions

<b>L</b>	1.6mm +/-0.2mm
<b>W</b>	3.2mm +/-0.2mm
<b>T</b>	0.8mm +/-0.1mm
<b>P</b>	0.8mm +/-0.1mm

#### Packaging Specifications

<b>Packaging:</b>	T&R, 180mm, Plastic Tape
<b>Packaging Quantity:</b>	4000

#### General Information

<b>Style:</b>	SMD Array
<b>Series:</b>	CA064
<b>Chip Size:</b>	0612
<b>Description:</b>	SMD, MLCC, Array, Flex Termination, Auto Grade
<b>Features:</b>	Automotive
<b>RoHS:</b>	Yes
<b>Termination:</b>	Tin
<b>Failure Rate:</b>	N/A
<b>Approvals:</b>	AEC-Q200
<b>AEC-Q200:</b>	Yes

#### Specifications

<b>Capacitance:</b>	2200 pF
<b>Capacitance Tolerance:</b>	10%
<b>Voltage DC:</b>	200 VDC
<b>Temperature Coefficient:</b>	X7R