


Ceramic, Commercial Grade, CA064, 3300 pF, 10%, 200 V, 0612, X7R, SMD, MLCC, Array, Flex Termination, Auto Grade



Dimensions

L	1.6mm +/-0.2mm
W	3.2mm +/-0.2mm
T	0.8mm +/-0.1mm
P	0.8mm +/-0.1mm

Packaging Specifications

Packaging:	T&R, 180mm, Plastic Tape
Packaging Quantity:	4000

General Information

Style:	SMD Array
Series:	CA064
Chip Size:	0612
Description:	SMD, MLCC, Array, Flex Termination, Auto Grade
Features:	Automotive
RoHS:	Yes
Termination:	Tin
Failure Rate:	N/A
Approvals:	AEC-Q200
AEC-Q200:	Yes

Specifications

Capacitance:	3300 pF
Capacitance Tolerance:	10%
Voltage DC:	200 VDC
Temperature Coefficient:	X7R