


Ceramic, Commercial Grade, CA064, 10 pF, 5%, 50 V, 0612, COG, SMD, MLCC, Array, Ultra-Stable, Class I



General Information	
Style:	SMD Array
Series:	CA064
Chip Size:	0612
Description:	SMD, MLCC, Array, Ultra-Stable, Class I
RoHS:	Yes
Termination:	Tin
Failure Rate:	N/A
Miscellaneous:	Note: Kemet 50 Volt parts may be operated in 63 volt applications

Dimensions	
L	1.6mm +/-0.2mm
W	3.2mm +/-0.2mm
T	0.8mm +/-0.1mm
P	0.8mm +/-0.1mm

Specifications	
Capacitance:	10 pF
Capacitance Tolerance:	5%
Voltage DC:	50 VDC
Temperature Coefficient:	COG

Packaging Specifications	
Packaging:	T&R, 180mm, Plastic Tape
Packaging Quantity:	4000